

PHILIPS

Headlight bulb

X-tremeVision

Type of lamp: H4

Pack of: 1

12 V,60/55 W



12342XVB1

Feel safe, drive safe

Boosts your vision on the road

Philips X-tremeVision halogen headlamp offers up to 100% more vision. X-tremeVision is engineered with state-of-the-art technology for ultimate bright light. It is ECE compliant for road legal use.

100% more light for maximum visibility*

- See further and react faster with up to 100% more vision

Enhancing safety with increased visibility

- Greater driving comfort and safety

Fully homologated, road-legal bright light

- Complying with high quality standards of ECE homologation

High quality and ultra resistant headlamp

- Philips is the choice of major car manufacturers
- Change both your headlamps simultaneously for more safety
- Award-winning car lamp manufacturer
- Philips car lamps are made of high-quality quartz glass^
- Philips car lamps are highly resistant against humidity^
- Philips car lamps are highly UV resistant
- Wide range of 12V lamps for all functions

Highlights

100% more vision on the road

Based on the unique product design, X-tremeVision is offering ultimate bright light on the road

High quality and visibility

X-tremeVision gives you faster reaction time thanks to an earlier recognition of obstacles and traffic signs. Light is a fundamental part of the driving experience and light is key in preventing accidents. This product actively prevents accidents by increasing overall visibility and road illumination.

ECE homologation

X-tremeVision is fully compliant to ECE for road-legal use.

Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offers all car specific functions : high beam, Low beam, front fog, front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights

Change by pairs



Highly recommended to change them by pairs for symmetric light performance

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Commended Car lamps



Our lamps are often commended by automotive experts.


High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, eliminating the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability to withstand increased pressure

inside the lamp, UV-quartz glass is able to produce more powerful lighting. ^Application varies per bulb type.

Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit. ^Application varies per bulb type

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass ideal for all driving conditions and ensures their longevity at the same time.

Specifications

Packaging Data

Packaging type: B1
EAN1: 8727900350388
EAN3: 8727900350395

Electrical characteristics

Voltage: 12 V
Wattage: 60/55 W

Lifetime

Life time: 450h

Light characteristics

Lumens: 1650 lm

Ordering information

Order entry: 12342XVB1
Ordering code: 35038830

Outerpack information

Gross weight per piece: 0.4 kg
Height: 14.2 cm
Length: 25.5 cm
Width: 14.1 cm

Product description

Type: H4
Application: High beam, Front fog light, Low beam
Designation: H4 X-tremeVision
Homologation ECE

Range: X-tremeVision

Technology: Halogen

Base: P43t-38

Packed product information

Gross weight per piece: 40 g
Height: 13.5 cm
Length: 10.6, 5 cm
Net weight per piece: 21.5 g
Pack Quantity / MOQ: 10
Width: 9.5 cm

Marketing specifications

Expected benefits: More light
Product highlight: 100% more vision

