

PHILIPS

Motorcycle
headlights

X-tremeVision Moto

Type of lamp: H4

Pack of: 1

12 V,60/55 W



12342XVBW



Feel safe, ride safe

Up to 100% more light

For maximum performance and safety, Philips X-tremeVision Moto bulbs are engineered with state-of-the-art technology to offer up to 100% more vision for riders who need to see farther.

State-of-the-art technology

- Philips is the choice of major motorbike manufacturers.
- Respecting high quality standards of the ECE homologation
- Unique filament design and optimized geometry

100% more vision on the road

- Up to 100% more vision on the road
- Better lifetime and durability
- Philips moto lamps are made of high-quality quartz glass
- Maximum brightness on the road

Highlights

ECE homologation

Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as well as in aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.


Manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Unique filament design

Thanks to an improved filament design, specific gas mixture and optimized geometry Philips X-tremeVision moto headlamps achieve unique brightness and durability.

100% more light on the road



Thanks to improved filament geometry and the use of unique gas compositions the X-tremeVision Moto headlamps project up to 100% more vision.

Better lifetime and durability

"Philips X-tremeVision Moto bulbs are designed with state-of-the-art technology which improves lifetime and durability. The bulbs are filled with a unique gas which reduces the deterioration of the lamp's filament and increases its lifetime."

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Maximum brightness

Based on a unique filament design and optimized geometry, X-tremeVision Moto lamps are engineered with state-of-the-art technology for ultimate performance and bright, white light where it matters the most.

Specifications

Packaging Data

Packaging type: Blister
EAN1: 8727900362299
EAN3: 8727900362305

Light characteristics

Lumens: 1650 ± 15% at 13,2V

Marketing specifications

Expected benefits: More light
Product highlight: Up to 100% more vision

Product description

Designation: H4 X-tremeVision Moto
Range: X-TremeVision Moto
Technology: Halogen
Base: P43t-38
Application: High beam, Low beam
Type: H4

Lifetime

Lifespan: 300h

Electrical characteristics

Voltage: 12 V
Wattage: 60/55 W

Ordering information

Ordering code: 36229930
Order entry: 12342XVBW

Packed product information

Gross weight per piece: 47.7 g
Height: 12.900 cm
Length: 9.500 cm
Net weight per piece: 23.5 g
Pack Quantity / MOQ: 10
Width: 4.860 cm

Outerpack information

Gross weight per piece: 477 g
Height: 13 cm
Length: 25.500 cm
Width: 19 cm

