

PHILIPS

Headlight bulb

WhiteVision

Type of lamp: H8

Pack of: 2

12 V,35 W



12360WHVS2



Safety has never been so attractive

Intense white Xenon effect

Philips WhiteVision lamps add an intense white Xenon look (4300K) to your car headlights for a premium driving experience at night. The increased brightness of up to 60% more light makes it the perfect combination of style and safety.

Maximum visibility, premium look

- A premium driving experience with intense white Xenon effect

4300K stylish white light for your car

- Crisp beam with intense white light

Increased brightness to combine style and safety

- Up to 60% more vision to maximize clarity

100% more vision on the road

- 100% road legal, 100% intense white light
- Philips car lamps are highly resistant
- Philips is the choice of major car manufacturers

Highlights

A 4300K driving experience



Philips WhiteVision headlights are the right choice for drivers who want to drive with style without compromising on safety. With a color temperature of close to Xenon headlamps, a stylish white cap and brighter light on the road, WhiteVision is the ultimate upgrade for your headlamps. The Philips patented 3rd generation coating technology is an evolutionary masterpiece making WhiteVision the first headlamp with a truly white light.

Crisp white beam

With 4,300K* white light (i.e. 40% whiter light than standard lamp), Philips WhiteVision headlights illuminate the road ahead with a crisp white beam that eliminates darkness instantly. The premium beam for a premium driving experience.

60% more light on the road

A longer beam pattern with 60%* more light enables you to see other road users more clearly. It improves safety, giving you more time to react to potential hazards on the road ahead.

100% road legal



WhiteVision is ECE certified and the first road-legal intense white light. It gives you the ultimate in high visibility without compromising safety by dazzling the car in front.

High quality, high resistance

UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of early failure. Philips UV-Quartz glass car lamps allow more pressure inside the lamp to produce a more powerful light and extended lifetime.

The car manufacturers' choice

For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Specifications

Product description

Technology: Halogen
Type: H8
Range: WhiteVision
Application: High beam, Low beam, Additional high beam, Front fog light
Designation: H8 WhiteVision
Homologation ECE
Base: PGJ19-2

Electrical characteristics

Voltage: 12 V
Wattage: 35 W

Light characteristics

Color temperature: up to 4300 K K

Ordering information

Order entry: 12360WHVS2

Packaging Data

Packaging type: S2A

Marketing specifications

Expected benefits: Style
Product highlight: 4300K, Intense white xenon effect

