



Philips Standard  
car headlight bulb

Type of lamp: H9

Pack of: 1  
12 V, 65 W

12361C1



## Feel safe, drive safe

### Philips standard lamps

Our Signaling lamps are the choice of major car manufacturers. They offer best in class quality at competitive price.

#### Original equipment manufacturer

- Philips is the choice of major car manufacturers

#### Wide range of 12V lamps

- Wide range of 12V lamps to meet all applications

#### Quality standards according to ECE regulations

- Respecting high quality standards of the ECE homologation

#### Change in pairs

- Change both your headlamps at once for more safety

# PHILIPS

car headlight bulb  
Type of lamp: H9 Pack of: 1, 12 V,65 W

# Specifications

## Electrical characteristics

- Voltage: 12 V
- Wattage: 65 W

## Packaging Data

- EAN1: 8711500475848
- EAN3: 8727900371000
- Packaging type: C1

## Product description

- Application: Low beam, Front fog
- Homologation ECE
- Range: Standard
- Technology: Halogen
- Type: H9
- Designation: 12361C1
- Base: PGJ19-5

## Outerpack information

- Gross weight per piece: 0.359 kg
- Height: 4.7 cm
- Length: 19.8 cm
- Width: 18.7 cm

## Packed product information

- Gross weight per piece: 28.9 g
- Height: 3.8 cm
- Length: 4.5 cm
- MOQ (for professionals): 10
- Net weight per piece: 22 g
- Pack Quantity: 1
- Width: 9 cm

## Ordering information

- Order entry: 12361C1
- Ordering code: 47584830

## Marketing specifications

- Expected benefits: Standard
- Product highlight: Philips standard lamps

## Lifetime

- Life time: up to 600 h

## Light characteristics

- Color temperature: 3400 K
- Lumens: 3000 lm

12361C1

# Highlights

## Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## ECE homologation

We are dedicated to producing best-in-class Philips automotive products and services in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000).

## Designed for multiple usage

Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

## Change in pairs

It is highly recommended to change them in pairs for symmetrical light performance.



Issue date 2019-07-05

Version: 5.0.1

12 NC: 8670 001 40628

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)