

Philips DiamondVision
car headlight bulb

H11

12V

55W

2x T10 LED lamps included

12362DVSL



Drive with style

Ultimate white light

Philips DiamondVision halogen headlamp is the ultimate style upgrade for your car with 5000K white light. With the specially designed blue coating, DiamondVision makes you stand out from the crowd.

Stylish white light to stands out

- Cool elegance for your headlights
- Bright white color match effect for high end look

High quality and ultra resistant headlamp

- Philips car lamps are made of high-quality quartz glass[^]
- Philips car lamps are highly resistant against humidity[^]
- Philips car lamps are highly UV resistant
- Change both your headlamps simultaneously for more safety
- Philips is the choice of major car manufacturers.

PHILIPS

car headlight bulb
H11 12V, 55W, 2x T10 LED lamps included

Highlights

5000K white light for style

Philips DiamondVision Vision headlight lamps provide the perfect choice for drivers who want a crisp white look for their headlights. DiamondVision provide a truly white light for great visibility and style.

High-end look car

Supplied with two colour matching T10 LED position lamps, DiamondVision gives your car lights the premium look of high end cars.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, eliminating the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability to withhold increased pressure inside the lamp, UV-quartz glass is able to produce more powerful lighting. ^Application varies per bulb type.

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit. ^Application varies per bulb type

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

Change by pairs



Highly recommended to change them by pairs for symmetric light performance

Car manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standards on modern automobiles. Today, one in two cars in Europe and one in three worldwide, is equipped with Philips lighting.

12362DVSL

Specifications

Packaging Data

- Packaging type: SL
- EAN1: 8727900354478
- EAN3: 8727900354485

Product description

- Technology: Halogen
- Application: Front fog light
- Range: DiamondVision
- Type: H11
- Homologation ECE: NO
- Designation: H11 DiamondVision
- Base: PGJ19-2

Electrical characteristics

- Voltage: 12 V
- Wattage: 55 W

Marketing specifications

- Expected benefits: Ultimate white light
- Product highlight: 5000K

Light characteristics

- Color temperature: up to 5000 K
- Lumens [lm]: 700 ±10%

Ordering information

- Order entry: 12362DVSL
- Ordering code: 35447830

Outerpack information

- Height: 12.6 cm
- Length: 27.6 cm
- Width: 22.8 cm
- Gross weight per piece: 2.53 kg

Packed product information

- Pack Quantity / MOQ: 20
- Gross weight per piece [g]: 126.5
- Height [cm]: 10.9
- Length [cm]: 10.9
- Net weight per piece [g]: 22
- Width [cm]: 5.3

Lifetime

- Life time: B3/Tc = 200/400



Issue date 2018-08-10

Version: 1.0.1

12 NC: 8670 001 55551

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com