

PHILIPS

car headlight bulb

X-tremeVision
Pro150

Type of lamp: H11

Pack of: 2

12 V, 55 W



12362XVPS2



Striking brightness for extra safety

The best blend of high performance and lifetime

Combining striking brightness with the kind of lifespan previously unavailable in such a high-performance bulb, Philips X-tremeVision Pro150 provides the visibility to keep you and your loved ones even safer on the road.

See the road better with up to 150% brighter light

- See more to drive safely

Longer lasting for a lifetime of safety

- Up to 450 hours¹ use from a high-performance bulb^{***}
- Don't compromise on safety, change in pairs

More contrast and visibility with cool light

- Cool light gives a clearer view and more comfort

The reassurance of Philips quality

- Philips is the choice of major car manufacturers

High-performance beam throws light 70 m further^{**}

- Give yourself more time to spot and avoid hazards

Highlights

Brighter light for more safety

With Philips X-tremeVision Pro150, you enjoy up to 150% brighter light. Drive home to your loved ones knowing you can see clearly even in darkness and adverse weather conditions. Advanced filament design provides greater precision and luminance for better illumination of the road, while new Diamond Precision quartz-glass technology ensures more brightness.

A lifetime of safety

The new production technique for Philips Diamond Precision quartz glass increases light throughput as well as providing greater resistance to thermal shock and pressure. A tailor-made composition of precious gases further protects the filament from ageing. That means more brightness and a longer lifespan of up to 450 hours (refers to H7; H1: 350h), probably the longest from such a powerful bulb.

Change both bulbs at once

It simply makes more sense to change headlamp bulbs in pairs, rather than only replacing the failed one. Modern bulbs provide increased light output and superior performance, offering a safer driving experience. By replacing bulbs in pairs, you save time and cost, avoid the risk of headlight failure, benefit from a brighter and better balanced beam, but above all, you make driving safer for yourself and your loved ones.

Stay alert for longer

Driving in dark conditions can be tiring to the eyes, leading to strained sight and a greater risk of fatigue. Projecting a whiter light of up to 3,400K (refers to H7; H1: 3,450K), Philips X-tremeVision Pro150 gives your view ahead greater contrast, which helps you identify and interpret approaching objects with increased confidence. Seeing more clearly keeps you alert for longer, making your drive safer and more enjoyable.

Highest quality car lighting

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Original Equipment Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Philips X-tremeVision Pro150 is compatible with car models of major brands, such as Audi, BMW, Ford, GM, Toyota and Volkswagen. See the product selector guide for more information.

See up to 70 meters further

Because it can throw light up to 70 meters further ahead on the road, Philips X-tremeVision Pro150 increases your ability to react to potential hazards. Extending your safety distance means you and your passengers can enjoy a safer drive.

Specifications

Electrical characteristics

Voltage: 12 V

Wattage: 55 W

Lifetime

Life time: 400 h

Light characteristics

Color temperature: 3,450 K

Lumens: 1,350 ±10%

Marketing specifications

Expected benefits: More light

Product highlight: Up to 150% brighter light

Ordering information

Order entry: 12362XVPS2

Ordering code: 01276030

Outerpack information

Gross weight per piece: 1.578 kg

Height: 12.0 cm

Length: 32.5 cm

Width: 24.2 cm

Packaging Data

EAN1: 8719018015778

EAN3: 8719018012777

Packaging type: S2

Packed product information

Height: 13.0 cm

Length: 10.6 cm

MOQ (for professionals): 10

Net weight per piece: 20.2 g

Pack Quantity: 2

Width: 5.6 cm

Product description

Application: High beam

Application 2: Low beam

Application 3: Front fog

Base: PGJ19-2

Designation: H112362XVP12V55WPGJ19-2S2

Homologation ECE

Range: X-tremeVision Pro150

Technology: Halogen

Type: H11

