

PHILIPS

Headlight bulb

Xenon Standard

Type of lamp: D5S

Pack of: 1

12 V,25 W

12410C1



Feel safe, drive safe

Original quality

Philips Xenon Standard is for replacement of the burned-out lamp. It is of the same quality and performance as the original equipped bulb

Original quality replacement for your headlight

- Xenon Standard is the original quality replacement option

Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

Original equipment manufacturer

- Adhering to high quality standards of the ECE homologation
- Philips car lamps are made of high-quality quartz glass
- Award-winning car lamp manufacturer
- Philips is the choice of major car manufacturers.
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

Highlights

Original quality replacement



Philips Xenon Standard offers the original quality light performance of a new car. The quality of the bulb is endorsed by all major car manufacturers.

Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. *compared to standard halogen bulbs

Car manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles - Philips is the inventor of Xenon HID technology. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

ECE homologation



Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as well as in after-sales market. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the

capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

Commended Car lamps



Our lamps are often commended by automotive experts.

Specifications

Marketing specifications

Expected benefits: Standard
Product highlight: Original quality

Product description

Technology: Xenon
Application: High beam, Low beam
Homologation ECE
Marking ECE: E4 0B7
Range: Xenon Vision
Type: D5S
Designation: D5S
Base: PK32d-7

Electrical characteristics

Wattage: 25 W
Voltage: 12 V

Light characteristics

Lumens: 2000lm +300/-200
Color temperature: 4200

Lifetime

Life time: B3/Tc = 2500/4000

Ordering information

Order entry: 12410C1
Ordering code: 37753833

Packaging Data

EAN1: 8727900377538
EAN3: 8727900377545
Packaging type: C1

Packed product information

Gross weight per piece: 225 g
Height: 8.05 cm
Length: 6.5 cm
Net weight per piece: 10.5 g
Pack Quantity / MOQ: 2
Width: 6 cm

Outerpack information

Gross weight per piece: 0.450 kg
Height: 11 cm
Length: 14 cm
Net weight per piece: 0.21 g
Width: 11.6 cm

