

PHILIPS

Xenon car headlight bulb

Xenon Vision

Type of lamp: D8S

Pack of: 1

42 V, 25 W

12411C1



Feel safe, drive safe

Ideal for replacement

Philips Xenon Vision replaces a single burnt-out lamp while matching the colour of the unchanged one thanks to its new single-lamp replacement technology. Therefore it is the ideal replacement lamp and is economical too!

The point of reference for xenon bulb replacement

- Xenon Vision perfectly matches the unchanged Xenon lamp

Xenon quality and ultra-resistant car bulb

- Philips car lamps are highly UV resistant
- Philips is the inventor of xenon HID technology

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Complying with the high quality standards

Highlights

Single-lamp replacement

Philips Xenon Vision replaces a single burnt-out lamp while matching the colour of the unchanged one. Its new single-lamp replacement technology allows for one-by-one replacement while still matching the colour temperature of the unchanged lamp. Thus, Xenon Vision is the perfect solution for single-lamp replacement.

UV Resistant

Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensuring their longevity.

Car manufacturers' choice

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. Philips Original Equipment Quality products are designed and developed following strict quality-control processes (including applicable ISO norms), leading to consistently high production standards.

ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Original Xenon technology

Xenon HID (High Intensity Discharge) lamps offer considerably more light for safer driving in all conditions. As a matter of fact, the intense white light produced by the xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

Specifications

Packaging Data

Packaging type: C1
EAN1: 8719018004673
EAN3: 8719018004680

Electrical characteristics

Voltage: 42 V
Wattage: 25 W

Light characteristics

Colour temperature: 4500 K
Lumens: 2000 lm

Ordering information

Order entry: 12411C1
Ordering code: 00467333

Outer pack information

Height: 5.7 cm
Length: 11.1 cm
Width: 9.6 cm
Gross weight per piece: 0.204 kg

Product description

Type: D8S
Application: High beam, Low beam
Homologation ECE
Range: Xenon Vision
Technology: Xenon
Designation: D8S Vision
Base: PK32d-1

Packed product information

Gross weight per piece: 97 g
Height: 9.3 cm
Length: 5.4 cm
Net weight per piece: 73.2 g
Width: 5.4 cm
MOQ (for professionals): 2
Pack Quantity: 1

Marketing specifications

Expected benefits: More light
Product highlight: Ideal for replacement

