

PHILIPS

Conventional Interior
and Signalling

SilverVision

Type of lamp: PY21W

Pack of: 2

12 V, 21 W

12496SVB2



Drive with style

Silver-coated design indicator

SilverVision signalling lamps are designed for drivers seeking to personalise their vehicles. With SilverVision, drivers enjoy a full Chrome effect in the front and rear indicators.

Chrome effect

- Indicator bulbs with Silver coating

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Change both indicator bulbs at once for maximum effect
- Wide range of 12-V lamps to meet all applications
- Respecting the high quality standards of ECE homologation

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Change in pairs

We highly recommend that you change your indicator bulbs in pairs for a symmetrical effect.

Designed for multiple usage



Which 12-V lamp for which application? Philips' Automotive offering includes the following applications: front and rear indicators.

ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Silver-coated design indicator

When turned off, Philips SilverVision bulbs prevent unaesthetic orange effects in the optics thanks to their unique Chrome coating. When turned on, they emit a homologated orange light.

Electrical characteristics

Voltage: 12 V

Wattage: 21 W

Lifetime

Life time: Up to 500 h

Light characteristics

Lumens: 280 lm

Packaging Data

EAN3: 8711500311191

EAN1: 8711500311177

Packaging type: B2

Product description

Application: Front indicator, Rear indicator

Base: BAU15s

Designation: PY21W SilverVision

Homologation ECE

Range: SilverVision

Technology: Conventional

Type: PY21W

Outer pack information

Gross weight per piece: 0.306 kg

Height: 13 cm

Width: 13.5 cm

Packed product information

Pack Quantity: 2

MOQ (for professionals): 20

Gross weight per piece: 15.3 g

Height: 12.9 cm

Length: 6.7 cm

Net weight per piece: 8 g

Width: 2.7 cm

Ordering information

Ordering code: 31117730

Order entry: 12496SVB2

Marketing specifications

Expected benefits: Style

