

PHILIPS

Conventional Interior
and Signaling

SilverVision

Type of lamp: PY21W

Pack of: 2

12 V, 21 W

12496SVB2



Drive with style

Silver coated design indicator

SilverVision signaling lamps are designed for drivers seeking to personalize their vehicles. With SilverVision, drivers enjoy a full Chrome effect in the front and rear indicators.

Chrome effect

- Indicator lamps with Silver coating

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Change both signaling lamps at once for maximum effect
- Wide range of 12V lamps to meet all applications
- Respecting the high quality standards of ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Change by pairs

We highly recommend to change your signaling bulbs by pairs for symmetric effect.

Designed for multiple usage



Which 12V lamp for which application? Philips Automotive offering includes the following applications: front and rear indicators.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Silver coated design indicator

When turned off, Philips SilverVision bulbs prevent from unaesthetic orange effect in optics thanks to its unique Chrome coating. When turned on, it emits an orange, homologated light.

Specifications

Electrical characteristics

Voltage: 12 V

Wattage: 21 W

Lifetime

Life time: Up to 500 h

Light characteristics

Lumens: 280 lm

Packaging Data

EAN3: 8711500311191

EAN1: 8711500311177

Packaging type: B2

Product description

Application: Front indicator, Rear indicator

Base: BAU15s

Designation: PY21W SilverVision

Homologation ECE

Range: SilverVision

Technology: Conventional

Type: PY21W

Outerpack information

Gross weight per piece: 0.306 kg

Height: 13 cm

Width: 13.5 cm

Packed product information

Pack Quantity: 2

MOQ (for professionals): 20

Gross weight per piece: 15.3 g

Height: 12.9 cm

Length: 6.7 cm

Net weight per piece: 8 g

Width: 2.7 cm

Ordering information

Ordering code: 31117730

Order entry: 12496SVB2

Marketing specifications

Expected benefits: Style

