

# PHILIPS

Conventional Interior  
and Signaling

VisionPlus

Type of lamp: P21W

Pack of: 2

12 V, 21 W

12498VPB2



## Feel safe, drive safe

Superior quality with enhanced visibility

VisionPlus lamps produce more powerful light output compared to standard. VisionPlus is the performance choice for safety-conscious drivers. Offering high performance and excellent value, it is the right choice for demanding drivers.

### Increased visibility

- More powerful light output

### Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all functions
- Respecting high quality standards of the ECE homologation

# Highlights

## Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

## Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog ,

front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## More powerful light output

Brake lighting is visible earlier, thanks to a more powerful light output. The following vehicle's breaking distance can be reduced by up to 3 meters at 100 km/h.

# Specifications

## Electrical characteristics

**Voltage:** 12 V

**Wattage:** 21 W

## Packaging Data

**EAN3:** 8727900363173

**EAN1:** 8727900363180

**Packaging type:** B2

## Product description

**Application:** Front indicator, Interior, License, Rear fog light, Rear indicator, Reversing light, Side indicator, Stop light, Boot light, Daytime running light, Tail light

**Base:** BA15s

**Designation:** P21W VisionPlus

**Homologation ECE**

**Range:** VisionPlus

**Technology:** Conventional

**Type:** P21W

## Outerpack information

**Gross weight per piece:** 0.3 kg

**Height:** 13.1 cm

**Width:** 13.5 cm

## Packed product information

**Pack Quantity:** 2

**MOQ (for professionals):** 20

**Gross weight per piece:** 15 g

**Height:** 12.9 cm

**Net weight per piece:** 7.7 g

## Ordering information

**Ordering code:** 36318030

**Order entry:** 12498VPB2

## Marketing specifications

**Expected benefits:** More light