



Philips Vision
Conventional Interior and
Signalling

Type of lamp: P21/5W
Pack of: 2
12 V, 21/5 W

12499B2



Feel safe, drive safe

Philips signalling lamps

Our Signalling lights are the choice of major car manufacturers. They offer best-in-class quality at a competitive price.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12 V lamps to meet all functions
- Respecting the high quality standards of ECE homologation

PHILIPS

Specifications

Electrical characteristics

- Voltage: 12 V
- Wattage: 5, 21 W

Lifetime

- Life time: Up to 250 h

Light characteristics

- Lumens: 440 lm

Packaging Data

- EAN3: 8711559520148
- EAN1: 8711500055453
- Packaging type: B2

Product description

- Application: Front indicator, Number plate, Rear fog light, Rear indicator, Rear position/parking light, Stop light, Daytime running light, Rear headlight
- Base: BAY15d
- Designation: P21/5 W
- Homologation ECE
- Range: Vision

- Technology: Conventional
- Type: P21/5 W

Outer pack information

- Gross weight per piece: 0.346 kg
- Height: 13.1 cm
- Length: 15 cm
- Width: 13.5 cm

Packed product information

- Pack Quantity: 2
- MOQ (for professionals): 20
- Gross weight per piece: 17.3 g
- Height: 12.9 cm
- Length: 6.7 cm
- Net weight per piece: 10 g
- Width: 2.7 cm

Ordering information

- Ordering code: 5545330
- Order entry: 12499B2

Marketing specifications

- Expected benefits: More light

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offering includes all car specific functions: high beam, low beam, front fog, front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, licence plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.



Issue date 2018-09-11

Version: 10.0.1

12 NC: 9246 295 17119
EAN: 87 11500 05545 3

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com