

PHILIPS

Conventional Interior
and Signaling

VisionPlus

Type of lamp: P21/5W

Pack of: 2

12 V, 21/5 W

12499VPB2



Feel safe, drive safe

Superior quality with enhanced visibility

VisionPlus lamps produce more powerful light output compared to standard. VisionPlus is the performance choice for safety-conscious drivers. Offering high performance and excellent value, it is the right choice for demanding drivers.

Increased visibility

- More powerful light output

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all functions
- Respecting high quality standards of the ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog ,

front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

More powerful light output

Brake lighting is visible earlier, thanks to a more powerful light output. The following vehicle's breaking distance can be reduced by up to 3 meters at 100 km/h.

Electrical characteristics

Voltage: 12 V

Wattage: 5, 21 W

Lifetime

Life time: Up to 2000h

Light characteristics

Lumens: 475 lm

Packaging Data

EAN3: 8727900363159

EAN1: 8727900363166

Packaging type: B2

Product description

Application: Front indicator, License, Rear fog light, Rear indicator, Rear position/ parking light, Stop light, Daytime running light, Tail light

Base: BAY15d

Designation: P21/5W VisionPlus

Homologation ECE

Range: VisionPlus

Technology: Conventional

Type: P21/5W

Outerpack information

Height: 13.1 cm

Width: 13.5 cm

Packed product information

Pack Quantity: 2

MOQ (for professionals): 20

Height: 12.9 cm

Net weight per piece: 10 g

Ordering information

Ordering code: 36316630

Order entry: 12499VPB2

Marketing specifications

Expected benefits: More light

