

PHILIPS

NORELCO

Wet & dry electric shaver, Series 8000

Shaver 8700

UltraTrack heads

GyroFlex 3D contouring system

50 min shaving, 1 hour charge

JetClean system

1250X/42



Series 8000 - Ultimate shaving experience with GyroFlex 3D and JetClean systems

The Philips Norelco Shaver 8700 (formerly called SensoTouch 3D) provides the ultimate shaving experience. The Gyroflex 3D system follows every contour of your face and the JetClean System washes, lubricates, dries and charges your shaver.

Designed for comfort

- Contour-following shaver minimizes pressure and irritation
- Smooth surface glides over your skin
- Skin friendly precision trimmer

Cordless, travel-friendly design

- One-hour charge provides up to 17 days of shaving time

Easy cleaning with Jet Clean

- Jet Clean system cleans, lubricates, and charges the razor

Innovative technology for a closer shave

- Shaving heads catch and trim every hair
- Shaver lifts hair to cut below skin level

Protective seal for wet or dry shaving

- Comfortable shaving, wet or dry, thanks to the AquaTec seal



asimpleswitch.com

Highlights

GyroFlex 3D



Philips Norelco's best shave yet, Series 8000 gives you the ultimate shaving experience. Its GyroFlex 3D system has three dynamic parts that move independently, flexing outward, pivoting around, and tilting inward to follow the contours of your face.

UltraTrack shaving heads



The UltraTrack shaving heads catch every hair in just a few strokes with three specialized shaving tracks: slots for long hairs, channels for longer hairs, and holes for the shortest stubble.

Super Lift and Cut action



The patented Super Lift & Cut dual blade system lifts hairs to cut comfortably below skin level for a close, even shave.

Aquatec - Wet or Dry shaving



With SensoTouch, you can shave any way you want. The AquaTec seal gives you the option of either a comfortable dry shave or a refreshing wet shave with shaving cream or gel. No matter which you choose, SensoTouch's slim, non-slip grip makes for easy handling.

SkinGlide shaving surface



With a low-friction SkinGlide shaving surface, the razor slides smoothly along your skin for a close shave without irritation.

Jet Clean system



SensoTouch is easy to maintain with a Jet Clean system that cleans, lubricates, and charges the shaver.

Great for travel

The SensoTouch 3D charges in one hour and provides up to 50 minutes (or a maximum of 17 days) of shaving time. A display lets you know

how much power remains in the lithium-ion battery and when you need to replace the blades. The SensoTouch 3D is completely cord free, has a travel lock, and comes with a protective pouch, so you can toss it in your bag, briefcase, or suitcase when you're on the go. Additionally, the razor features a worldwide voltage function that adjusts automatically from 100 volts to 240 volts AC, making the SensoTouch 3D ideal for international travel.

Precision trimmer



The unique skin friendly precision trimmer system is built to avoid unnecessary skin contact. Easy to use for perfect moustache and sideburn trimming.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Shaving Performance

Contour following: GyroFlex 3D contour following

Shaving system: UltraTrack shaving heads, Speed XL shaving heads, DualPrecision System, Patented Super Lift & Cut

Styling: Skin friendly precision trimmer

SkinComfort: SkinGlide

Ease of use

Charging: 1 hour, Rechargeable, Cordless, Quick charge

Shaving time: Up to 17 days

Display: 3 level battery indicator, Battery low indicator, Charge indicator, Travel lock, Cleaning indicator, Replace shaving heads

indicator

Wet & Dry: Wet and dry use, Jet Clean

Cleaning: Washable

Jet Clean: Cleans, lubricates and charge

Design

Handle: Slim handle, Easy grip, Anti-slip grip

Finishing: Ruby black frame, LED Display

Color: Black

Accessories

Stand: Charging stand

Pouch: Soft pouch

Maintenance: Cleaning brush, Protective cap

Jet Clean

Power

Battery Type: Lithium-ion

Run time: 50 min

Automatic voltage: 100–240 V

Stand-by power: 0.15 W

Max power consumption: 5,4 W

Service

2-year guarantee

Replacement head: Replace every yr with RQ12

