



Philips Vision
Conventional Interior and
Signalling

Type of lamp: BAX

Pack of: 10
12 V, 1.3 W

12628CP



Feel safe, drive safe

Philips signalling lamps

Our signalling lamps are the choice of major car manufacturers. They offer best-in-class quality at a competitive price.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12 V lamps to meet all functions
- Respecting the high-quality standards of the ECE homologation

PHILIPS

Specifications

Electrical characteristics

- Voltage: 12 V
- Wattage: 1.3 W

Lifetime

- Life time: 1200 hrs

Light characteristics

- Lumens: 6.5 lm

Packaging Data

- EAN3: 8711500779397
- EAN1: 8711500774323
- Packaging type: CP

Product description

- Application: Interior
- Base: BX8.4d light green
- Designation: BX8.4D olive green
- Homologation ECE: NO
- Range: Vision

- Technology: Conventional
- Type: BAX

Outer pack information

- Gross weight per piece: 0.308 kg
- Height: 11.6 cm
- Length: 16.9 cm
- Width: 10.4 cm

Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 50
- Gross weight per piece: 1.54 g
- Net weight per piece: 0.9 g

Ordering information

- Ordering code: 77432373
- Order entry: 12628CP

Marketing specifications

- Expected benefits: More light

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offering includes all car specific functions: high beam, low beam, front fog, front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, licence plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.



Issue date 2017-03-13

Version: 5.0.1

12 NC: 9247 557 17110
EAN: 87 11500 77434 7

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com