

PHILIPS

Motorcycle
headlights

PremiumVision
Moto

Type of lamp: HS1

Pack of: 1

12 V,35/35 W



12636C1

+3

Feel safe, ride safe

Up to 30% more vision

Producing up to 30% more vision than a standard lamp, Vision Moto headlamps allow motorcycle riders to see farther with improved light beam performance at a very competitive price. For greater safety, choose Vision Moto bulbs!

The most economical choice

- The best value choice

30% more vision than a standard lamp

- 30% more vision
- Philips moto lamps are made of high-quality quartz glass

State-of-the-art technology

- Philips is the choice of major motorbike manufacturers.
- Respecting high quality standards of the ECE homologation


Highlights

Best value



The Philips Vision Moto lamps are the best choice for drivers looking for economical lamp solutions and not willing to compromise on security. The motorcycle bulbs offer 30% more vision on the road than a standard lamp.

Greater light-beam projection



Offering 30% more vision on the road, Philips PremiumVision Moto headlamps are the perfect choice for motorcycle riders seeking for light performance and safety. With better light output, riders can react faster to obstacles and avoid accidents.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

ECE homologation

Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as well as in aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.

Specifications

Marketing specifications

Expected benefits: More light
Product highlight: Up to 30% more vision

Product description

Designation: HS1 Vision Moto
Range: PremiumVision Moto
Technology: Halogen
Application: High beam, Low beam
Base: PX43t
Type: HS1

Ordering information

Order entry: 12636C1
Ordering code: 51250130

Packaging Data

Packaging type: Carton
EAN1: 8711559512501
EAN3: 8727900370881

Electrical characteristics

Voltage: 12 V
Wattage: 35/35 W

Outerpack information

Gross weight per piece: 705 g
Height: 7.8 cm
Length: 23.8 cm
Width: 9.3 cm

Packed product information

Gross weight per piece: 705 g
Height: 7.6 cm
Length: 4.55 cm
Pack Quantity / MOQ: 10
Width: 4.55 cm

Lifetime

Life time: 400h

