

PHILIPS

Motorcycle
headlights


CityVision Moto

Type of lamp: HS1

Pack of: 1

12 V, 35/35 W

12636CTVBW



Feel safe, ride safe

Up to 40% more vision

For better safety and visibility in city traffic, Philips has designed CityVision Moto lamps, which produce up to 40% more light to see further. CityVision Moto bulbs also project a distinctive, attention-grabbing orange effect in the headlight.

State-of-the-art technology

- Adhering to the high quality standards of ECE homologation
- Philips moto lamps are made of high-quality quartz glass
- Philips is the choice of major motorcycle manufacturers.

Be seen in traffic

- Distinctive orange effect in the headlight
- Designed for city riders
- 40% more vision on the road

Vibration resistance

- Vibration resistance up to 10G

Highlights

Distinctive orange effect



Philips CityVision Moto headlights have been specifically developed for city riders. Thanks to their distinctive orange effect, Philips motorcycle bulbs grab the attention of drivers and guarantee earlier recognition of the rider.

Designed for city use



Philips CityVision Moto headlights are specifically designed to improve the rider's safety in a city environment. The attention-grabbing orange effect and the 40% increase in light output allow a safer riding experience in traffic and play an active role in accident reduction.

ECE homologation



Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as

well as in after-sales market. Our products are manufactured from high-quality materials and tested to the highest specifications to maximise the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.

Greater light-beam projection

Offering 40% more vision on the road, the Philips CityVision Moto headlights actively participate in increasing the rider's security. Thanks to better visibility on the road Philips motorcycle lamps allow for better obstacle recognition and accident prevention.

High-quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2650° C and glass 800° C) are able to withstand severe thermal shock. With the capability for increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Manufacturers' choice

For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that

have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Vibration resistant



Philips CityVision Moto lamps are designed with state-of-the-art technology to resist vibrations up to 10G and last longer. Those motorcycle bulbs are mounted with an extremely resistant double coil filament to withstand a wide range of vibrations including physical shocks.

Specifications

Electrical characteristics

Voltage: 12 V
Wattage: 35/35 W

Marketing specifications

Expected benefits: More light
Product highlight: See and be seen

Product description

Designation: HS1 CityVision Moto
Range: CityVision Moto
Technology: Halogen
Base: PX43t
Application: High beam, Low beam
Type: HS1

Lifetime

Lifespan: 400h

Light characteristics

Lumens: 825 ±15%
Colour temperature: Up to 3200 K

Ordering information

Ordering code: 39894630
Order entry: 12636CTVBW

Outer pack information

Gross weight per piece: 463 g
Height: 13 cm
Length: 25.500 cm
Width: 19 cm

Packaging Data

Packaging type: Blister
EAN1: 8727900398946
EAN3: 8727900398953

Packed product information

Gross weight per piece: 46.3 g
Height: 12.900 cm
Length: 9.500 cm
Net weight per piece: 22 g
Pack Quantity / MOQ: 10
Width: 4.860 cm

