



Philips DiamondVision
Moto
Headlight bulb

Type of lamp: HS1

Pack of: 1
12 V,35/35 W

12636DVB1

Ride with style

5000K Ultimate white light for your stylish ride

Philips DiamondVision Moto halogen headlamp is the ultimate style upgrade for your motorcycle with 5000K white light. With the specially designed blue coating, DiamondVision Moto makes you stand out from the crowd.

5000 K white light for your stylish ride

- DiamondVision Moto lights up your motorcycle

State-of-the-art technology

- Philips moto lamps are made of high-quality quartz glass[^]
- Philips moto lamps are highly resistant against humidity[^]
- Philips car lamps are highly UV resistant

High quality and ultra resistant headlight

- Philips is the choice of major motorcycle manufacturers.

PHILIPS

Headlight bulb
Type of lamp: HS1 Pack of: 1, 12 V,35/35 W

Specifications

Marketing specifications

- Expected benefits: White light
- Product highlight: Ultimate 5000K white light

Product description

- Designation: HS1 DV
- Range: DiamondVision moto
- Technology: Halogen
- Base: P32d
- Application: High beam, Low beam
- Type: HS1

Electrical characteristics

- Voltage: 12 V
- Wattage: 35/35W W

Light characteristics

- Color temperature: up to 5000 K K
- Lumens: 390 ± 8% / 250 ± 8% lm

Lifetime

- Life time: 400h

Packaging Data

- Packaging type: B1
- EAN1: 8711500781482
- EAN3: 8711500781499

Ordering information

- Ordering code: 78148230
- Order entry: 12636DVB1

Packed product information

- Gross weight per piece: 76.5 g
- Height: 12.9 cm
- Length: 9.5 cm
- Net weight per piece: 21.5 g
- Pack Quantity / MOQ: 1
- Width: 5 cm

Outerpack information

- Gross weight per piece: 0.765 g
- Height: 14.6 cm
- Length: 25.9 cm
- Net weight per piece: 215 g
- Width: 20.1 cm

12636DVB1

Highlights

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass ideal for all driving conditions and ensures their longevity at the same time.

5000K for style upgrade

Based on the special complete blue coating design, DiamondVision Moto is offering ultimate white light of 5000K, bringing style to your headlights

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability to withhold increased pressure inside the lamp, UV-quartz glass is able to produce more powerful lighting. ^Application varies per bulb type.

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit. ^Application varies per bulb type

Manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standards on modern automobiles. Today, one in two cars in Europe and one in three worldwide, is equipped with Philips lighting.



Issue date 2020-02-03

Version: 3.0.1

12 NC: 8670 001 56374

© 2020 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com