

PHILIPS

Motorcycle
headlights

Vision Moto

Type of lamp: S2

Pack of: 1

12 V, 35/35 W

12728C1



Feel safe, ride safe

Up to 30% more vision

Producing up to 30% more vision than a standard light, Vision Moto headlights allow motorcycle riders to see further with improved light beam performance at a very competitive price. For greater safety, choose Vision Moto bulbs!

The most economical choice

- 30% more vision
- The best value choice

30% more vision than a standard lamp

- Philips moto lamps are made of high-quality quartz glass

State-of-the-art technology

- Philips is the choice of major motorbike manufacturers.
- Respecting the high quality standards of ECE homologation

Highlights

Best value




The Philips Vision Moto lamps are the best choice for drivers looking for economical lamp solutions and not willing to compromise on security. The motorcycle bulbs offer 30% more vision on the road than a standard lamp.

ECE homologation

Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as well as in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximise the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.

Greater light-beam projection



Offering up to 30% more vision on the road, Philips VisionMoto headlamps are the perfect choice for motorcycle riders seeking light

performance and safety. With better light output, riders can react faster to obstacles and avoid accidents.

High-quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2650^o C and glass 800^o C) are able to withstand severe thermal shock. With the capability for increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Manufacturers' choice

For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Specifications

Electrical characteristics

Voltage: 12 V

Wattage: 35/35 W

Marketing specifications

Expected benefits: More light

Product highlight: Up to 30% more vision

Product description

Designation: S2 Vision Moto

Range: Vision Moto

Technology: Halogen

Base: BA20d

Application: High beam, Low beam

Type: S2

Lifetime

Lifespan: Up to 400 h

Light characteristics

Lumens: 825 ±15%

Ordering information

Ordering code: 77359330

Order entry: 12728C1

Outer pack information

Gross weight per piece: 211 g

Height: 7.8 cm

Length: 23.8 cm

Width: 9.3 cm

Packaging Data

Packaging type: C1

EAN1: 8711500773593

EAN3: 8711500779342

Packed product information

Gross weight per piece: 211.67 g

Height: 7.6 cm

Length: 4.55 cm

Pack Quantity / MOQ: 10

Width: 4.55 cm

