



Philips X-tremeUltinon  
LED  
car signalling bulb

LED-T20-AMB [~WY21W]

Number of bulbs: 2  
12 V, amber intense  
Advanced automotive system



12763X2

## Brighter and more stylish

Strong, durable and vibrant LED signalling

For safe and modern driving, change to intense amber Philips X-tremeUltinon LED indicators [~WY21W]. They are powerful, precise and look good, so you can signal in safety and with style.

### Brighter LED exterior lights

- Signal your intent with brighter exterior lighting
- Intense amber indicators to be seen better

### Upgrade your style

- Upgrade your lights, upgrade your style

### Superior light diffusion

- Uniform light distribution for enhanced visibility

### Longer-lasting LED lights

- Durable and long-lasting LED lighting

### Exceptional Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

# PHILIPS

## Highlights

### Bright and vibrant signals

Signalling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather conditions reduce visibility, the need for bright and vibrant signalling becomes even more important. Philips X-tremeUltinon LED signalling lights provide you with bright daylight effect and up to 6000 K for reverse and positioning lights. With more intense colours for indicating and stop applications, instantly on LEDs and a uniform and well-directed light, you'll give other drivers vital extra time to react to your movements.

### Stylish signalling colours

While the main goal of exterior lighting is to help you see and be seen, there is no reason why you should not look good at the same time. If you are looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for indicators and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signalling LED lights.

### Intense amber indicators

Philips LED indicators feature vibrant amber colour performance that make your intentions clear to surrounding traffic. Amber intense means more safety for you and others around you.

### Uniform light distribution

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signalling light is projected where you need it (whether that is reversing, stopping, or signalling). With wide angle and uniform light diffusion, not only

can you see more of the road, other drivers can see more of you.

### Automotive-grade quality

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. Philips Automotive-Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips bulbs, because when you buy Philips, you buy quality. You get powerful bright light and precise beam performance. You get high-end style. And you get an advanced LED lighting system for a safer, smoother and more enjoyable drive.

### Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease. However, it's recommended that you get your new Philips X-tremeUltinon LED lights installed by specialist mechanics – they will make sure you're ready to go. While these lamps are compatible with a wide range of existing car models, not all car types are supported.

### Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. And Philips X-tremeUltinon LED lights are extremely durable. Due to the latest technological innovation, they prevent heat and vibrational damage and last up to 12 years. With most cars replaced or upgraded within that time, your stylish new lights should last you the lifetime of your car.

## Specifications

### Packaging Data

- Packaging type: X2
- EAN1: 8727900395778
- EAN3: 8727900395785

### Product description

- Range: X-tremeUltinon LED
- Technology: LED
- Type: WY21W
- Application: Indicator
- Homologation ECE: NO
- Marking ECE: -

### Electrical characteristics

- Voltage: 12 V
- Wattage: 5.5 W

### Marketing specifications

- Expected benefits: Advanced automotive system

### Light characteristics

- Colour temperature: Amber
- Lumens: 180 lm

### Ordering information

- Order entry: 12763X2
- Ordering code: 39577830

### Outer pack information

- Gross weight per piece: 0.6 kg
- Height: 8.5 cm
- Length: 19.5 cm
- Width: 15.1 cm

### Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- MOQ (for professionals): 20
- Pack Quantity: 2
- Width: 2.8 cm

### Lifetime

- Life time: Up to 12 years



Issue date 2018-11-29

Version: 8.0.1

12 NC: 8670 001 17218

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* This LED retrofit light is specifically designed and intended for off-road use only. It is your own responsibility that the use of the LED retrofit light complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability.

\* Important: This LED retrofit light is specifically designed and intended for off-road use only, such as rally and race track driving, and is therefore subject to a technical check for installation. The LED retrofit light cannot legally be installed in on-road vehicles.

\* Lumileds cannot accept any responsibility and/or liability. It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Designed for rally and race tracks. Not for use on public roads.

\* The LED retrofit headlights and exterior signalling lighting cannot be sold in Germany, Spain, Slovakia, Cyprus, UK, Netherlands, Czech Republic, Greece, Hungary, Latvia, Luxembourg, Malta and Slovenia.