

# PHILIPS

Interior and  
signaling bulb

X-tremeUltinon LED

T10

White 6700K

35 lumen

Position light

127976700KX2



## Maximum road safety and style

### Sparkling bright effect

Sparkling bright LED exterior car light, the perfect color match with Xenon and LED car headlights. 360° uniform light diffusion. 12 years lifetime, with extreme heat and vibration resistance.

#### **Sparkling bright effect**

- Sparkling bright effect

#### **360° uniform light diffusion**

- 360° uniform light diffusion

#### **Maximum road safety**

- ECE beam pattern compliant (front positioning function)\*

#### **12 year lifespan**

- 12 year lifespan
- 3 year limited warranty for consumer usage

# Highlights

## Sparkling bright effect

Bright white 6700K LED car light, the perfect color match with Xenon and LED Headlights

## 360° uniform light diffusion

360° optical design for uniform light diffusion.

## ECE beam pattern compliant

Similar or better beam pattern than standard halogen lamp, to not glare other road users \*  
There is no ECE regulation existing for LED bulbs. ECE beam pattern compliance is tested on several commonly used luminaires where the LED bulb beam pattern matches the ECE approved halogen beam pattern

## 12 year lifespan



High heat and vibration resist

## 3 year limited warranty



3 year limited warranty for consumer usage

# Specifications

## Product description

Technology: LED

Application: Parking light, Interior light

Base: W2.1X9.5D

Range: X-tremeUltinon LED

Type: T10

Color temperature: White 6700K

Lumens: 35 lm

Voltage: 12 V

Wattage: 0.05 W

Lifespan: 12 years

## Marketing specifications

Expected benefits: Maximum road safety and style

Product highlight: Sparkling bright LED car light

## Logistic data

Quantity in box: X2

Reference: 127976700KX2

EAN (Japan): 8727900393477

Ordering code (Japan): 39347730

