



Philips X-tremeUltinon
LED
Signaling bulb

LED-T10 [~W5W]

Number of bulbs: 1
12 V, 6500 K cool blue
Interior, license plate

127996500KX1

Brighter and more stylish

Design your interior with brighter LED lights

Never lose your keys again with bright, stylish and durable Philips LED 30mm Festoons for interior lighting. Strong light for 6000 K daylight effect illuminates the inside of your car, while being kind on your eyes.

Brighter LED interior lights

- Bright interior lights to see everything inside your car

Stylish visual upgrade

- Bright lights for the interior of your car
- Upgrade your lights, upgrade your style

Longer lasting LED lights

- Durable and long-lasting LED lighting

Exceptional Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

PHILIPS

Signaling bulb
LED-T10 [-W5W] Number of bulbs: 1, 12 V, 6500 K cool blue, Interior, license plate

Specifications

Packaging Data

- EAN1: 8727900398335
- Packaging type: X1

Product description

- Technology: LED
- Application: Interior, License plate
- Range: X-tremeUltinon LED
- Type: W5W
- Homologation ECE: NO
- Base: W2,1x9,5d
- Designation LED Type: LED-T10 [-W5W]
- Technical features: CeraLight

Electrical characteristics

- Voltage: 12 V

Marketing specifications

- Expected benefits: interior
- Product highlight: Brighter, vibrant signals

Light characteristics

- Color temperature: Up to 6500K
- Lumens [lm]: 50

Ordering information

- Order entry: 127996500KX1
- Ordering code: 39833530

Outerpack information

- Height: 8.5 cm
- Length: 19.5 cm
- Width: 15.1 cm
- Gross weight per piece: 0.37 kg

Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- Width: 2.8 cm
- MOQ (for professionals): 20
- Pack Quantity: 2

Lifetime

- Life time: Up to 12 years

127996500KX1

Highlights

See more inside your car

Whether it's your phone, your keys or your child's missing left shoe, at some point we've all had to search for a misplaced item in a poorly lit car. With Philips LED interior lighting, you get a warm, bright and uniformly diffused light. So the next time you're searching around in the trunk, the glove compartment or the floor of your car, you'll be able to see exactly what you're doing and find anything with ease.

Stylish interior lighting

Interior lighting is not just about function and comfort; it's about looking good too. Upgrade your interior lighting with a brighter warm light or daylight effect. So when you open the trunk, or fire up the dashboard lights, you can do so with a little extra style. Your car is an expression of who you are, so make a style statement with Philips interior LED lights.

Bright interior light

Whether for dome or reading lights, the glove box or the trunk, your light requirements and taste may differ. For the interior of your car, you can select from a variety of Philips X-tremeUltinon LED lamps for superior visibility and style. Choose from a comfortable warm white (4000 Kelvin) and daylight effect (6000 Kelvin). Bright and stylish, this light will change your driving experience. Whether you're searching for a dropped phone, your passengers want to read, or you're trying to work out the best route to your destination, you can now do so with a bright interior light.

Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. And Philips X-tremeVision LED exterior lights are extremely durable. Due to the latest technological innovation, they prevent heat and vibrational damage and last up to 12 years. With most cars replaced or upgraded within that time, your stylish new exterior lights should last you the lifetime of your car.

Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style. And you get an advanced LED lighting system for a safer, smoother and more enjoyable drive.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.



Issue date 2019-01-30

Version: 4.1.1

12 NC: 8670 001 53209

© 2019 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.