



Philips X-tremeUltinon  
LED  
Interior and signaling bulb

**T10**  
White 6700K  
50 lumens  
License plate & Interior light

127996700KX1

# Maximum road safety and style

## Sparkling bright effect

Sparkling bright LED exterior car light. 360° uniform light diffusion. 12 years lifetime, with Philips CeraLight technology.

### Sparkling bright effect

- Sparkling bright effect

### 360° uniform light diffusion

- 360° uniform light diffusion

### Maximum road safety

- ECE beam pattern compliant (front positioning function)\*

### 12 year lifespan

- Philips CeraLight™ technology
- 3 year limited warranty for consumer usage

# PHILIPS

Interior and signaling bulb  
T10 White 6700K, 50 lumens, License plate & Interior light

127996700KX1

## Specifications

### Packaging Data

- EAN1: 8727900398335

### Product description

- Technology: LED
- Application: Interior light, License plate light
- Base: W2.1X9.5D
- Range: X-treme Ultinon LED, X-tremeUltinon LED
- Type: T10
- Color temperature: White 6700K
- Lumens: 50 lm
- Voltage: 12 V
- Wattage: 1 W
- Homologation ECE: NO
- Marking ECE: -
- Lifespan: 12 years

### Electrical characteristics

- Wattage: 0.9 W

### Marketing specifications

- Expected benefits: Maximum road safety and style
- Product highlight: Sparkling bright LED car light

### Light characteristics

- Color temperature: 6500 K

### Ordering information

- Order entry: 127996500KX1

### Logistic data

- Quantity in box: X1
- Reference: 127996700KX1
- EAN (Japan): 8727900393651
- Ordering code (Japan): 39365130

## Highlights

### Sparkling bright effect

Bright white 6700K LED car light, the perfect color match with Xenon and LED Headlights

### 360° uniform light diffusion

360° optical design for uniform light diffusion.

### ECE beam pattern compliant

Similar or better beam pattern than standard halogen lamp, to not glare other road users \* There is no ECE regulation existing for LED bulbs. ECE beam pattern compliance is tested on several commonly used luminaires where the LED bulb beam pattern matches the ECE approved halogen beam pattern

### 12 year lifespan

Philips CeraLight™ patented technology ensures ultra-long LED service life thanks to: o optimal thermal properties, for maximum cooling of the LED o high resistance to shock and vibrations, with heat-sink base design o perfect insulation from short-circuit

### 3 year limited warranty



3 year limited warranty for consumer usage



Issue date 2019-09-20

Version: 13.2.1

12 NC: 8670 001 27326

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.