



Philips Vision LED
car interior and signalling
bulb

LED-FEST [38 mm]

Number of bulbs: 1
12 V, 6000 K, daylight effect
Experience more light



128016000KX1

Bright interior lighting

See more with LED

Never lose your keys again with bright, stylish and durable Philips LED 38-mm Festoons for interior lighting and licence plates. Strong light for 6000-K daylight effect illuminates the inside of your car, while being kind on your eyes.

Upgrade your style

- Upgrade your lights, upgrade your style

Bright LED interior lights

- Bright interior lights to see everything inside your car

Long-lasting LED lights

- Durable and long-lasting LED lighting

Good light diffusion

- Good light distribution for enhanced visibility

Durable Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

PHILIPS

car interior and signalling bulb
LED-FEST [38 mm] Number of bulbs: 1, 12 V, 6000 K, daylight effect, Experience more light

Specifications

Packaging Data

- EAN1: 8727900395853
- EAN3: 8727900395860
- Packaging type: X1

Product description

- Technology: LED
- Application: Interior, Trunk, glove compartment
- Range: Vision LED
- Type: Festoon

Marketing specifications

- Expected benefits: Experience more light

Ordering information

- Order entry: 128016000KX1
- Ordering code: 39585330

Outer pack information

- Height: 8.5 cm
- Length: 19.5 cm
- Width: 15.1 cm
- Gross weight per piece: 0.27 kg

Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- Width: 2.8 cm
- MOQ (for professionals): 10
- Pack Quantity: 1

Lifetime

- Life time: Up to 8 years

128016000KX1

Highlights

Stylish interior light

Your light requirements and taste may differ depending on the application. For the interior of your car, you can select from a variety of Philips Vision LED lamps for more brightness. Select a comfortable warm white (4000 Kelvin). Your car is an expression of who you are, so make a style statement with Philips interior LED lights.

See more inside your car

Whether it is your phone, your keys or your child's missing left shoe, at some point we have all had to search for a misplaced item in a poorly lit car. With Philips LED interior lighting, you get a warm, bright and uniformly diffused light. So the next time you're searching around in the boot, the glove compartment or on the floor of your car, you will be able to see exactly what you are doing and find anything with ease.

Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That is a major weakness of conventional lights: the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Vision LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance, with a lifetime of up to 8 years.

Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signalling light is projected where you need it (whether that is reversing, stopping or signalling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

Automotive-grade quality

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light. You get high-end style.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.



Issue date 2018-11-29

Version: 3.0.1

12 NC: 8670 001 46605

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* This LED retrofit light is specifically designed and intended for off-road use only. It is your own responsibility that the use of the LED retrofit light complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability.

* Important: This LED retrofit light is specifically designed and intended for off-road use only, such as rally and race track driving, and is therefore subject to a technical check for installation. The LED retrofit light cannot legally be installed in on-road vehicles.

* Lumileds cannot accept any responsibility and/or liability. It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Designed for rally and race tracks. Not for use on public roads.

* The LED retrofit headlights and exterior signalling lighting cannot be sold in Germany, Spain, Slovakia, Cyprus, UK, Netherlands, Czech Republic, Greece, Hungary, Latvia, Luxembourg, Malta and Slovenia.