

PHILIPS

Conventional Interior
and Signalling

Vision

Type of lamp: R10W

Pack of: 10

12 V, 10 W

12814CP



Feel safe, drive safe

Philips signalling lamps

Our Signalling lights are the choice of major car manufacturers. They offer best-in-class quality at a competitive price.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12 V lamps to meet all functions
- Complying with the high quality standards of ECE homologation

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offering includes all car specific functions: high beam, low beam, front fog, front

indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, licence plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Electrical characteristics

Voltage: 12 V
Wattage: 10 W

Lifetime

Life time: Up to 625 h

Light characteristics

Lumens: 125 lm

Packaging Data

EAN3: 8711500773388
EAN1: 8711500486141
Packaging type: CP

Product description

Application: Interior, Number plate, Rear indicator, Rear position/parking light, Reversing light
Base: BA15s
Designation: R10W
Homologation ECE
Range: Standard
Technology: Conventional
Type: R10W

Outer pack information

Gross weight per piece: 1.704 kg
Height: 13.1 cm
Length: 28.9 cm
Width: 13.5, 18.8 cm

Packed product information

Pack Quantity: 1
MOQ (for professionals): 200
Height: 12.9 cm
Length: 2.75 cm
Net weight per piece: 5.93 g
Width: 2.38 cm

Ordering information

Ordering code: 48614173

Marketing specifications

Expected benefits: Standard

