



Philips X-treme Ultinon
LED
Car lamps

Multi-sockets room lamp
White 6500K
100 lumens
High Color Rendering LED



12823HCRIX1

Bright modern interior

True colors in your car's interior

High Color Rendering (90+CRI) LED interior car light, reveals clear and vivid interior and objects' colors, with less blue light, for better eyes comfort. Uniform light diffusion. Long lasting LED with 12 years lifetime.

True color rendering

- High CRI LED, to reveal true colors in your car's interior

Less blue light emission

- Less blue light emission

Easy installation

- Multi-sockets installation options

12 year lifespan

- 12 year lifespan
- 3 year limited warranty for consumer usage

PHILIPS

Car lamps

Multi-sockets room lamp White 6500K, 100 lumens, High Color Rendering LED

Specifications

Product description

- Technology: LED
- Application: Interior light
- Base: SV8.5-8, w2.1x9.5d, Ba9s
- Range: X-treme Ultinon LED
- Type: Multi-sockets room lamp
- Color temperature: White 6500K
- Lifespan: 12 years
- Lumens [lm]: 100
- Voltage [V]: 12
- Wattage [W]: 1.1

Marketing specifications

- Expected benefits: Bright modern interior

Logistic data

- EAN: 8727900395488
- Ordering code: 39548830
- Quantity in box: X1
- Reference: 12823HCRIX1

12823HCRIX1

Highlights

True color rendering

CRI (color rendering index) is a measure of how accurately a light is rendering objects' true colors. Standard LED interior light may make colors to appear unnatural. Philips high 90+CRI LED light allows objects' colors to appear clear and vivid, improving their appearance.

Less blue light emission

Blue light waves creates a glare that can reduce visual contrast and affect sharpness and clarity. This also may be one of the reasons for eyestrain, headaches, physical and mental fatigue. Sources of blue light includes computer screen, electronic devices, fluorescent-light and LED lights. Philips high 90+CRI LED light emits less blue light than standard LED interior light, for better eyes comfort.

Multi-sockets installation

Supplied with multi-socket options, to easily replace room lamp types T10 and festoon 30mm

12 year lifespan



High heat and vibration resist

3 year limited warranty



3 year limited warranty for consumer usage



Issue date 2018-01-18

Version: 5.0.1

12 NC: 8670 001 37707
EAN: 87 27900 39548 8

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com