



Philips DayLightGuide
LED Daytime running lights

Daylight Guide
12 V
15 W



12825WLEDX1

Exclusive design signature, maximum visibility

to drive with safety and style

The new generation of high-power Luxeon LED daytime running lights improve your safety and style on the road, increasing your visibility day and night.

Exclusive design signature

- Homologated lightguide technology

Original Equipment Quality

- High-quality aluminium housing
- Water and gravel-impact resistant

24h visibility

- Dimmable: stays on night & day
- High power new generation LED
- Wide angle to be seen better

Easy installation for all cars

- Hybrid and electric car compatible
- Smart clip-on system

PHILIPS

Highlights

Clip-on system



Simple installation with smart clip-on system. Install the brackets in any cavity and simply click the modules into place. The modules will lock tightly and are free from theft.

Dimmable



Our Daylight solution stays on day and night. During the day, LED Daylight makes cars more visible and more rapidly detectable by the drivers of other vehicles or pedestrians moving in the opposite direction, which, as a whole, increases road safety. The system automatically dims at night.


Aluminum housing



The robust high-quality aluminium housing prevents corrosion and is weatherproof:

water, salt, sand and dust stand no chance. The result is long life and no maintenance work.

Gravel-impact resistant



The high-quality aluminum housing and lens are water and gravel-impact resistant. After mounting the system does not require any maintenance.

High power new generation LED



High power new generation LED

Homologated lightguide



The lightguide technology delivers a distinct lighting signature. Contrary to the dot appearance of earlier solutions, the light that is guided through the 2 beams is uniform and extends to a wider angle. As any other Philips


solution the beam complies with all homologation standards.

Hybrid & electric compatible



The Philips Daytime Running Light range is compatible with hybrid and electric car technology.

Wide angle



The homologated Lightguide technology results in a uniform light diffusion without dots and an ultra-wide beam.

Specifications

Maximum visibility

- Intensity (DRL): 550 cd
- Intensity (position light): 80 cd
- Color temperature: 6000 K
- Beam angle: 150 % wider than standard
- LED lifetime: 5000 hours

Easy to install

- Clip-on system
- Start & stop compatible: with ACC control

Robustness

- Premium finishing: High quality aluminum housing
- Gravel-impact resistant: Automotive test PSA B21 7090
- DRL set resistant to: water, salt, dust & sand

Technical specifications

- Application: Day light
- Homologation: ECE R87
- Consumption (DRL): 2 x 7.7 W
- Consumption (Position light): 2 x 2.4 W

Ordering information

- Order entry: 12825WLEDX1
- Ordering code: 38638733

Packaging Data

- EAN1: 8727900386387
- EAN3: 8727900386394

Product description

- Technology: LED
- Homologation ECE
- Voltage [V]: 12



Issue date 2018-03-16

Version: 7.1.4

12 NC: 9237 988 1010
EAN: 87 27900 38638 7

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com