

PHILIPS

Car Lamp

X-tremeUltinon LED

Type of lamp: T16

Pack of: 1

12 V



12832X1



Maximum road safety and style

High intensity white LED exterior car light for reverse function. Maximum visibility and safety, to see and be seen better. Extreme heat and vibration resistance for ultra-long service life.

Intense bright light

- Intense bright light

Maximum road safety

- ECE beam pattern compliant*

12 year lifespan

- 12 year lifespan
- 3 year limited warranty for consumer usage

Highlights


Intense bright light



T16
Halogen standard

High power xenon white LED car light, to see and be seen better.

ECE beam pattern compliant*



Similar or better beam pattern than standard halogen lamp, to see and be seen better.

12 year lifespan



High heat and vibration resist

3 year limited warranty



3 year limited warranty for consumer usage

Specifications

Packaging Data

Packaging type: Blister

Green Specifications

Heavy metals: Cd free, Hg free, Pb free

Product description

- Technology: LED
- Application: Reversing light
- Base: W2.1X9.5D
- Range: X-tremeUltinon LED
- Type: T16
- Color temperature: White 6700K
- Lifespan: 12 years
- Lumens: 200 lm
- Voltage: 12 V
- Wattage: 3.4 W

Marketing specifications

- Expected benefits: High-Performance LEDs
- Product highlight: Intense bright LED car light

