

PHILIPS

car signalling bulb

Vision LED

LED-RED [~P21W]

Number of bulbs: 2

12 V, red intense

Experience more light



12839REDX2



Bright signals. Stylish driving.

Durable LED quality

For a stylish drive, benefit from signalling lights with intense colours. Philips Vision LED [~P21W] stop lights are bright, intense red and look good, so you can signal in safety and with style.

Upgrade your style

- Upgrade your lights, upgrade your style

Brighter LED exterior lights

- Brighter signals for improved safety
- Instantly on lights make rapid braking safer

Longer-lasting LED lights

- Durable and long-lasting LED lighting

Good light diffusion

- Good light distribution for enhanced visibility

Durable Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

Highlights

Stylish signalling colours

While the main goal of exterior lighting is to help you see and be seen, there is no reason why you should not look good at the same time. If you are looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for indicators and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signalling LED lights.

Be seen with bright signals

Signalling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signalling light ensures you are seen for improved safety. Whether it's reversing, positioning or stopping, Philips Vision LED signalling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

Instantly on brake lights

Incandescent lamps take time to light up and reach peak performance. LED lights, on the other hand, are "instantly on". The difference is measured in fractions of a second. Under hard braking, fractions of a second matter. For example, at 60 mph (100 km/h), just four tenths of a second difference in reaction time equates to an extra 11 metres of reaction distance – that's about 2.5 car lengths of extra thinking time. With Philips LED stop lights, as soon as you decide to brake, the driver behind will know.

Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signalling light is projected where you need it (whether that is reversing, stopping or signalling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

Automotive-grade quality

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light and precise beam performance. You get high-end style.

Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That is a major weakness of conventional lights: the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Vision LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance, with a lifetime of up to 8 years.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.

Specifications

Packaging Data

EAN1: 8727900395815
EAN3: 8727900395822
Packaging type: X2

Product description

Technology: LED
Application: Stop
Range: Vision LED
Type: P21W

Marketing specifications

Expected benefits: Experience more light

Ordering information

Order entry: 12839REDX2
Ordering code: 39581530

Outer pack information

Height: 8.5 cm
Length: 19.5 cm
Width: 15.1 cm
Gross weight per piece: 0.6 kg

Packed product information

Height: 9.2 cm
Length: 6.8 cm
Width: 2.8 cm
MOQ (for professionals): 20
Pack Quantity: 2

Lifetime

Life time: Up to 8 years



- * This LED retrofit light is specifically designed and intended for off-road use only. It is your own responsibility that the use of the LED retrofit light complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability.
- * Important: This LED retrofit light is specifically designed and intended for off-road use only, such as rally and race track driving, and is therefore subject to a technical check for installation. The LED retrofit light cannot legally be installed in on-road vehicles.
- * Lumileds cannot accept any responsibility and/or liability. It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Designed for rally and race tracks. Not for use on public roads.
- * The LED retrofit headlights and exterior signalling lighting cannot be sold in Germany, Spain, Slovakia, Cyprus, UK, Netherlands, Czech Republic, Greece, Hungary, Latvia, Luxembourg, Malta and Slovenia.