



Philips X-tremeUltinon
LED
car signaling bulb

LED-WHITE [~P21W]

Number of bulbs: 2
12 V, 6000 K daylight effect
Reverse



12898X2



Brighter and more stylish

Strong, durable and vibrant LED signaling

For safe and modern driving, change to bright Philips X-tremeUltinon LED P21W reverse signals. They are powerful, precise and look good so you can signal in safety and with style.

Exceptional Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

Superior light diffusion

- Uniform light distribution for enhanced visibility

Upgrade your style

- Upgrade your lights, upgrade your style

PHILIPS

car signaling bulb
LED-WHITE [-P21W] Number of bulbs: 2, 12 V, 6000 K daylight effect, Reverse

12898X2

Specifications

Packaging Data

- EAN (Japan): 39345330
- EAN1: 8727900393453

Product description

- Technology: LED
- Application: Reversing light
- Color temperature: White 6000K
- Range: X-treme Ultinon LED, X-tremeUltinon LED
- Base: BA15S
- Lifespan: 12 years
- Lumens [lm]: 380
- Type: P21W
- Voltage [V]: 12
- Wattage [W]: TBD
- Homologation ECE: NO
- Marking ECE: -

Electrical characteristics

- Wattage: 4.3 W

Marketing specifications

- Expected benefits: Maximum road safety and style
- Product highlight: Intense bright LED car light

Light characteristics

- Color temperature: 6000 K

Ordering information

- Order entry: 12898X2

Logistic data

- Quantity in box: X1
- Reference: 12898X2

Highlights

Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style. And you get an advanced LED lighting system for a safer, smoother and more enjoyable drive.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible headlights with ease. However, it's recommended that you get your new Philips LED headlights installed by specialist mechanics – they will make sure you're ready to go. While these headlights are compatible with a wide range of existing car models, not all car types are supported.

Stylish signaling colors

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

Uniform light distribution

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide angle and uniform light diffusion, not only can you see more of the road, other drivers can see more of you.



Issue date 2019-09-20

Version: 16.2.1

12 NC: 8670 001 20154

© 2019 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.