

PHILIPS

Conventional Interior
and Signaling

BlueVision

Type of lamp: T4W

Pack of: 2

12 V,4 W

12929BVB2



Drive with style

Ultimate brightness and unique stylish blue light

BlueVision signaling and interior bulbs are designed for drivers seeking to personalize their vehicles. With BlueVision signaling and interior lamps, drivers enjoy a blue xenon effect unmatched in a fully homologated road-legal lamp.

The best blue Xenon effect

- Xenon blue effect

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all applications
- Respecting high quality standards of the ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Xenon blue effect

Philips interior and signaling lamps are the best choice for driver seeking a stylish effect. The cool white light provides greater visibility in all car applications (License plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights).

Electrical characteristics

Voltage: 12 V

Wattage: 4 W

Lifetime

Life time: 875h

Light characteristics

Lumens: 35, 50 lm

Packaging Data

Packaging type: B2

EAN1: 8711500310316

EAN3: 8711500310392

Product description

Application: License, Rear position/ parking light, Side indicator, Boot light, Glove compartment light, Reading light, Tail light

Base: BA9s

Designation: T4W BlueVision

Homologation ECE

Range: BlueVision

Technology: Conventional

Type: T4W

Outerpack information

Gross weight per piece: 0.186 kg

Height: 13 cm

Length: 15 cm

Width: 13.5 cm

Packed product information

Gross weight per piece: 9.3 g

Height: 12.9 cm

Length: 6.7 cm

Net weight per piece: 2 g

Width: 2.7 cm

Ordering information

Ordering code: 31031630

Order entry: 12929BVB2

Marketing specifications

Expected benefits: Style

