

# PHILIPS

Conventional Interior  
and Signalling

Vision

Type of lamp: T4W

Pack of: 10

12 V, 4 W

12929CP



## Feel safe, drive safe

### Philips signalling lamps

Our Signalling lights are the choice of major car manufacturers. They offer best-in-class quality at a competitive price.

#### **Original Equipment manufacturer**

- Philips is the choice of major car manufacturers
- Wide range of 12 V lamps to meet all functions
- Complying with the high quality standards of ECE homologation

# Highlights

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offering includes all car specific functions: high beam, low beam, front fog, front

indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, licence plate lights, rear position/parking light, interior lights.

## ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Electrical characteristics

**Voltage:** 12 V

**Wattage:** 4 W

## Lifetime

**Life time:** Up to 1250 h

## Light characteristics

**Lumens:** 35 ± 15% at 13.5 V lm

## Packaging Data

**EAN3:** 8711500220622

**EAN1:** 8711500220608

**Packaging type:** CP

## Product description

**Application:** Number plate, Rear position/parking light, Side indicator, Boot light, Glove compartment light, Reading light, Rear headlight

**Base:** BA9s, PG13

**Designation:** T4W

**Homologation ECE**

**Range:** Standard

**Technology:** Conventional

**Type:** T4W

## Outer pack information

**Gross weight per piece:** 0.55, 0.169 kg

**Height:** 11.6 cm

**Length:** 16.9 cm

**Width:** 10.4 cm

## Packed product information

**Pack Quantity:** 1

**MOQ (for professionals):** 200

**Gross weight per piece:** 2.75 g

**Net weight per piece:** 2 g

**Width:** 2.1 cm

## Ordering information

**Ordering code:** 22060873

**Order entry:** 12929CP

## Marketing specifications

**Expected benefits:** Standard

