

PHILIPS

Conventional Interior
and Signaling

LongLife EcoVision

Type of lamp: W5W

Pack of: 2

12 V,5 W

12961LLECOB2



Drive with care

Higher lifetime, less replacement

Tired of changing your signaling and interior bulbs all the time? With higher lifetime of a car bulb, Philips LongLife EcoVision is the choice for drivers seeking to minimise maintenance on their vehicles.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all functions
- Respecting high quality standards of the ECE homologation

Lasts significantly longer than a standard lamp

- Extended lifetime for better value

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog ,

front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Extended lifetime

LongLife EcoVision signaling and interior lights are the best choice for drivers seeking optimal value. Their increased lifetime combined with high heat and vibration resistance guarantees a hassle free drive for extended periods of time.

Electrical characteristics

Voltage: 12 V

Wattage: 5 W

Lifetime

Life time: Up to 2000h

Packaging Data

EAN3: 8727900382051

EAN1: 8727900382044

Packaging type: B2

Product description

Application: Interior, License, Side indicator, Stop light, Boot light, Door light, Entry light, Glove compartment light, Reading light, Tail light

Base: W2,1x9,5d

Designation: W5W

Homologation ECE

Range: LongLife EcoVision

Technology: Conventional

Type: W5W

Outerpack information

Gross weight per piece: 0.195 kg

Height: 12 cm

Length: 15 cm

Width: 12 cm

Packed product information

Pack Quantity: 2

MOQ (for professionals): 20

Height: 13.5 cm

Length: 0.95 cm

Net weight per piece: 1.13 g

Width: 9.5 cm

Ordering information

Ordering code: 38204430

Marketing specifications

Expected benefits: Long lasting

