

# PHILIPS

Motorcycle  
headlights

CrystalVision ultra

Type of lamp: H7

Pack of: 1

12V, 55W

More style



12972CVUBW



## Ride with style

### Bright white light

Philips CrystalVision ultra moto halogen headlamp upgrades the style of your motorcycle with a bright white light.

#### **White modern xenon look**

- Bright white light for a stylish xenon look

#### **High-quality and ultra-resistant headlamp**

- Philips moto lamps are made of high-quality quartz glass
- Respecting the high quality standards of ECE homologation
- The favoured choice of major motorcycle manufacturers

# Highlights

## White light for motorcycle

CrystalVision ultra moto is a unique halogen lamp that offers a bright white light. High-tech and efficient to differentiate and personalise your motorcycle, with better visibility and comfort.

## High-quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. So Philips quartz-glass lamps (filament 2 650°C and glass 800°C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a

more powerful light. And more powerful light means an enhanced driving experience, however dark the road in front of you.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality materials and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Manufacturers' choice

For over 100 years, Philips bulbs have been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard in modern vehicles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

12972CVUBW

# Specifications

## Packaging Data

EAN1: 8711500221186  
EAN3: 8711500221193  
Packaging type: BW

## Light characteristics

Colour temperature: Up to 3700 K

## Marketing specifications

Expected benefits: More style

## Product description

Range: CrystalVision ultra Moto  
Technology: Halogen  
Application: High beam, Low beam  
Type: H7  
Homologation ECE  
Base: PX26d  
Designation: 12972CVUBW

## Electrical characteristics

Voltage: 12 V  
Wattage: 55 W

## Ordering information

Ordering code: 22118630  
Order entry: 12972CVUBW

## Packed product information

MOQ (for professionals): 10  
Pack Quantity: 1  
Gross weight per piece [g]: 34.9  
Height [cm]: 12.9  
Length [cm]: 9.5  
Net weight per piece [g]: 10.3  
Width [cm]: 3.5

## Outer pack information

Gross weight per piece [kg]: 0.350  
Height [cm]: 13  
Length [cm]: 19  
Width [cm]: 19

