

PHILIPS

car headlight bulb

RacingVision GT200

Type of lamp: H7

Pack of: 2

12V, 55W



12972RGTS2



Incredible performance from a road-legal bulb Let our lights take your driving to the next level

If you're passionate about driving, let Philips RacingVision GT200 car bulbs elevate your automotive experience. Up to 200% brighter light that shines over 80 meters longer means better vision and faster reactions for a more exciting drive.

Up to 200% brighter lights to transform your drive

- New bulb coating techniques maximize light throughput
- New quartz glass technology for ultra-precise light output
- See a step change in visibility and driving excitement

The best-performing beam in our portfolio

- Striking beam throws light up to 80 meters further**

Fully road-legal for an enjoyable drive

- High-performance light approved for use on public roads

The reassurance of Philips quality

- Philips is the choice of major car manufacturers

Highlights

Our best-performing bulb

The highest performer in our portfolio, Philips RacingVision GT200 delivers the super-bright visibility of a rally bulb in a format you can use on public roads. Experience the razor-sharp clarity of up to 200% brighter light. The optimized bulb design provides higher luminance for a better view of the road ahead, giving you a safer, more exciting drive.

More light on the road

New patented gradient and screen-print coating techniques enable these bulbs to project more light onto the road, improving your visibility in night-time driving conditions. In addition to maximized throughput, enjoy a stylish, distinctive light that's right on trend.

Brightness where you need it

New production techniques for Philips Diamond Precision quartz glass ensure a sharp cutoff line and a brighter sweetspot, giving you more brightness where it counts. Also, quartz glass means greater resistance to thermal shocks to protect the bulb's lifespan and enhanced UV absorption protects your headlight optics.

Extend your beam by 80 meters

With its ultra high-performance beam reaching a full 80 meters further than the legal minimum, Philips RacingVision GT200 lets you see more of the road ahead. Spot potential hazards sooner, react faster and position your car more accurately on the road. It all adds up to a safer, more satisfying driving experience.

Road-legal performance bulbs

Philips RacingVision GT200 headlight bulbs are ECE homologated for the road. Performance-oriented drivers enjoy a bright, vibrant and street-legal bulb compliant with relevant regulations.

Highest quality car lighting

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Original Equipment Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Philips RacingVision GT200 is compatible with car models of major brands, such as Audi, BMW, Ford, GM, Toyota and Volkswagen. See the product selector guide for more information.

Specifications

Electrical characteristics

Voltage: 12 V
Wattage: 55 W

Lifetime

Life time: 250h

Light characteristics

Color temperature: 3500
Lumens: 1500 ±10%

Marketing specifications

Expected benefits: More light
Product highlight: Up to 200% brighter light

Ordering information

Order entry: 12972RGTS2
Ordering code: 01262330

Outerpack information

Gross weight per piece: 1.380 kg
Height: 12.0 cm
Length: 32.5 cm
Width: 24.2 cm

Packaging Data

EAN1: 8719018012623
EAN3: 8719018012630
Packaging type: S2

Packed product information

Height: 13.0 cm
Length: 10.6 cm
MOQ (for professionals): 10
Net weight per piece: 10.3 g
Pack Quantity: 2
Width: 5.6 cm

Product description

Application: Low beam, High beam, Front fog
Base: PX26d
Designation: H7 12972 RGT 12V 55W PX26d S2
Homologation ECE
Range: RacingVision GT200
Technology: Halogen
Type: H7

