

14HT3154 (TXT) 14HT3304 (TXT + Clock + Radio)

TV ProPlus range

Equipped for small and medium sized Hotels and other Hospitality businesses



- **UIR-Link+ for Set-top Box Control***
 - **Radio: FM Built-in***
 - **Clock: Large Front LED Display***
 - **Wake Up Alarm With LED Indication***
 - **Multi Language Teletext Reception**
 - **Teletext Lockout**
 - **Wireless Smart-Loader™ Fast Reliable Clone Programming Capability**
 - **Sleep Timer**
 - **Welcome Message Selection**
 - **Front Control Lockout**
 - **Electronic Program Guide**
 - **Programmable Channel Blanking**
 - **Auto Power On**
 - **Volume Control Locking Features**
 - **Switch On Channel Programming**
 - **Audio/Video Muting**
 - **ESP™ (Energy Savings Programmability)**
 - **Low Battery Detection For Remote Control**
 - **Multiple Remote Control Support**
 - **Security Menu Access**
 - **Consumer Television Convertible**
 - **Head Phone Connection**
 - **External Speaker Connection**
- * 14HT3304 only*



PHILIPS

14HT3154 (TXT)

14HT3304 (TXT + Clock + Radio)



The ProPlus line offers a wider range of functions aimed at maximising management efficiency while guaranteeing the perfect convenience for guests.

Product Information

Colour

Blue Silver

Chassis

Type: IL01

Picture

Tube Category: 14" Hibri/37 cm
Visual Screen: 34 cm
Smart picture

Sound

Sound Power: 2 W Mono
Loudspeakers: 1 On Board Speaker

Reception

PLL digital tuning
UVSH tuner
127 presets
Dynamic Program Differentiation
WST 1 Page TXT

Connections

Front: Headphone out (3.5mm jack)
Rear: TV aerial Input (75 Ω coax)
Ext loudspeakers (3.5mm jack)
RJ II connector
Euro A/V connector
Radio-FM aerial connector

Miscellaneous

14HT3154 'ON' Power consumption:
36 W; Stand-by consumption: 5 W
14HT3304 'ON' Power consumption:
37 W; Stand-by consumption: 7,5 W

Mains: AC 220-240 ± 10%
Frequency: 50/60 Hz
Net Weight: 9 Kg.
TV set Dimensions: (W x H x D mm)
380 x 350 x 380
Ambient temperature: + 5° to 45°C

Product Highlights

Integrated FM radio 14HT3304

The Radio is accessed directly and simply by the RC.

LED Clock 14HT3304

The built-in clock, which is also an alarm, eliminates the need for an additional clock with cables and connections in the room.

Wireless Smart-Loader™

Provides the ability to copy all programming settings from one set into additional sets. This feature ensures uniformity between sets and significantly reduces installation time.

Hotel-Mode features

- **Front Control locking:** this feature locks all front controls, preventing guests from adjusting any television setting.
- **Programmable Channel Blanking:** provides a means to force the picture to be blanked without affecting the audio. Perfect for audio-only services (e.g. FM radio).
- **Volume Control Locking Feature:** this feature forces the TV set to operate within a user defined volume range preventing volume adjustments.
- **Switch On Channel:** it forces the television to a specified channel when turned on. Perfect for in-house advertising or information channels.

Multi Language Teletext reception with Lockout option

Guests can be served in their own teletext language. For each channel Western/ Eastern European, Turkish, Greek, Cyrillic or Arabic characters are available. Teletext Lockout option to simply block all access to teletext information.

Auto Power On

Forces the default power setting to the ON position after a power interruption or preventing sets from being turned off while in use.

Audio/Video Muting

Automatically detects a loss of television signal and optionally mutes both audio and video.

Electronic Program Guide

Provides guest with onscreen directory listing number and network affiliation. Channel guide is accessed via the touch of a single button on the remote control.

ESP™ (Energy Saving Programmability)

Energy Saving system that powers television off after a specified period of use. A simple countdown clock can be selectively set to operate from 0-99 hours with automatic clock reset at each power up.

Low Battery detection Remote Control

This feature informs hotelier the need to replace RC batteries to pre-empt guest complain.

External Speaker connection

Easy installation of speaker to bathroom via rear connector.

Welcome Message

A welcome greeting (max. 2 line with 20 characters each) is displayed on the screen each time the set is switched on.

Consumer Television Convertible

Easily converts to true consumer television for after-market sales.

UIR-Link+ 14HT3304

Makes it possible to connect a Set-top box to the tv and let the STB control the tv. Tamperproof, allows PREVIEW function, no tuner required in the STB, one remote control STB and tv.

Multiple Remote Control support

The tv can be easily configured to listen to 1 of 4 different remote controls. Allows the simultaneous use of up to 4 tvs in a single room.



RC2885/01

Type	Version	Transmission System	Destination
14HT3154-14HT3304	/01	PAL BG, SECAM L/L', PAL-I, BG/DK	Continental W. Europe + Eastern Europe + UAE
14HT3154-14HT3304	/05	PAL-I, SECAM L/L' PAL BG	United Kingdom + Ireland

Specifications subject to change without notice.

