



Philips Ultinon LED  
Car signaling bulb

## 168ALED-AMBER

Number of bulbs: 2  
12 V, amber intense  
Experience more light



168AULAX2

# Bright signaling. Stylish driving.

## Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips 168ALED for turn signaling are bright, vibrant amber and look good so you can signal in safety and with style.

### Stylish look

- Signal your intent with LED exterior lighting
- Intense amber turn signals to be seen better

### Brighter LED exterior lights

- Upgrade your lights, upgrade your style

### Long lasting LED lights

- Instant-on Performance
- Good light distribution for enhanced visibility

### Good light diffusion

- Philips automotive lighting at the highest quality level

### Durable Philips quality

- Easy installation and compatible with many car models
- Durable and long-lasting LED lighting

# PHILIPS

Car signaling bulb  
168ALED-AMBER Number of bulbs: 2, 12 V, amber intense, Experience more light

# Specifications

## Packaging Data

- EAN1: 46678721847
- EAN3: 50046678721842
- Packaging type: X2

## Product description

- Technology: LED
- Application: Side indicator
- Range: Ultinon LED
- Type: T10
- Homologation ECE: NO
- Base: W2.1X9.5D
- Designation LED Type: 168ALED-AMBER
- Technical features: Instant-on

## Electrical characteristics

- Voltage: 12 V

## Marketing specifications

- Expected benefits: Experience more light
- Product highlight: Bright signaling, Stylish Drive

## Light characteristics

- Color temperature: Amber intense
- Lumens [lm]: 230

## Ordering information

- Order entry: 168AULAX2
- Ordering code: 78721842

## Outerpack information

- Gross weight per piece [lbs]: 0.82
- Height [in]: 3.35
- Length [in]: 7.68
- Width [in]: 5.94

## Packed product information

- MOQ (for professionals): 10
- Pack Quantity: 2
- Gross weight per piece [lbs]: 0.01
- Height [in]: 3.62
- Length [in]: 2.68
- Width [in]: 1.1

## Lifetime

- Life time: Up to 8 years

168AULAX2

# Highlights

## Stylish exterior light

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

## Stylish signaling colors

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling lights ensures you are seen for improved safety. Whether it's reversing, turning, or stopping, Philips Ultinon LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

## Vibrant amber turn signals

Philips LED turn signals feature vibrant amber color performance that make your intentions clear to surrounding traffic. Amber intense means more safety for you and others around you.

## Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

## Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

## Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.

## Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional lights: the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Ultinon LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance, with a lifetime of up to 8 years.

## Excellent Light Distribution

The bright output and intense color adds more than just style. They provide superior light distribution, with a wide angle beam on the road so you can see and be seen better.



Issue date 2019-01-31

Version: 3.1.1

12 NC: 8670 001 50904

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.