

17" TFT LCD SXGA monitor



Ultra Slim Frame

- 17-inch color LCD monitor with excellent display performance
- Dual input- accepts DVI-D digital and VGA analog inputs
- Embedded AC power supply
- Advanced AUTO adjustment optimizes picture quality
- Adjustable tilt and swivel function
- sRGB compliant



Optional Multimedia Audio Module (AG3P48)

All accessories might not available in all market. Please check with your local philips representative for availability.



PHILIPS

17" TFT LCD SXGA monitor



Technical Specifications

LCD panel

- Type TFT LCD
- Screen size 17 inch / 43.2 cm
- Pixel pitch 0.264 x 0.264mm
- LCD panel type 1280 x 1024 pixels, R.G.B vertical stripe, Anti-glare polarizer, hard coated
- Effective viewing area 337.9 x 270.3mm
- Display colors 8 bits interface (16M colors)

Scanning

- Vertical refresh rate 56~76 Hz
- Horizontal frequency 30~82 KHz

Video

- Video dot rate 135 MHz
- Input impedance
 - video 75 ohm
 - Sync 2K ohm
- Input signal levels 0.7Vpp
- Sync input signal
 - Separate sync
 - Composite sync
 - Sync on green
- Sync polarities Positive and negative
- Video interface Dual input: D-Sub (analog) and DVI-D (digital) are available and user selectable

Optical characteristics

- Contrast ratio 400 (typ.)
- Brightness 260 cd/m² (typ.)
- Peak contrast angle 6 o'clock
- White chromaticity
 - x: 0.283 y: 0.297 (at 9300°K)
 - x: 0.313 y: 0.329 (at 6500°K)
- Viewing angle (C/R >5)
 - Upper ≥ 80°(typ.)
 - Lower ≥ 80°(typ.)
 - Left ≥ 80°(typ.)
 - Right ≥ 80°(typ.)
- Response time ≤25 ms (typ.)

Resolution & preset modes

- Maximum 1280x1024 at 75Hz
 - Recommended 1280x1024 at 60Hz
 - 33 user definable modes
 - 15 factory preset modes:
- | | H.freq (KHz) | V.freq (Hz) |
|-------------|--------------|-------------|
| 640 x 350 | 31.5 | 70 |
| 720 x 400 | 31.5 | 70 |
| 640 x 480 | 31.5 | 60 |
| 640 x 480 | 35.0 | 67 |
| 640 x 480 | 37.5 | 75 |
| 800 x 600 | 35.2 | 56 |
| 800 x 600 | 37.9 | 60 |
| 800 x 600 | 46.9 | 75 |
| 832 x 624 | 49.7 | 75 |
| 1024 x 768 | 48.4 | 60 |
| 1024 x 768 | 60.0 | 75 |
| 1152 x 870 | 69.0 | 75 |
| 1152 x 900 | 71.8 | 76 |
| 1280 x 1024 | 63.9 | 60 |
| 1280 x 1024 | 80.0 | 75 |
- (Interlace mode is not applicable)

Plug and play compatibility

- Display data channel DDC 2B (VESA)
- Microsoft® Windows® 95/98/ Me & 2000/ XP compatible

Power management

- Complies with EPA Energy Star and NUTEK specifications
- Typical operation 40W (typical)
- Sleep mode 1W

Low-emission characteristics

- Complies with TCO 95, MPRII and prEN50279 (so call MPRIII) specifications

Monitor controls and functions

- Front
 - Power on/off - Tact Switch
 - OK - Tact Switch
 - Auto - Tact Switch
 - Up/Down (Brightness) - Tact Switch
 - Left / Right - Tact Switch
- LED indicator
 - Green power on
 - Amber power save/OFF mode
 - Flashing Green new mode

Connections and cables

- Connections on monitor body
 - Video 15-pin D-sub (analog) DVI-D (digital)
 - DC output 12V, 6.5mm DC connector
 - Power IEC/CEE-22 type male power inlet on monitor body
- Cables D-Sub video cable, Power cord

User Options Accessories (sold separately)

- Multimedia Audio Module (AG3P40 Silver)
- Stereo 2W RMS
- User installation
- Power ON/OFF & Volume control
- DC +12V/500mA power in from Philips LCD monitor

Regulatory approvals

- TÜV/GS, TÜV-Ergo
- FCC-B, UL, CSA
- SEMKO
- prEN50279 Low Emission
- CE Mark
- NUTEK, Energy Star
- TCO '95

Physical specifications

- Dim. incl. base (WxHxD) 375 x 393 x 180 mm
- Dim. excl. base (WxHxD) 375 x 326 x 60 mm
- Tilt / Swivel -5°~35° / ± 175°
- Weight 5.0 Kg
- Power supply 100 – 240 VAC, 50/60 Hz
- Power consumption 40 W* (typ.)
- Temperature (operating) +5°C to +35°C
- Temperature (Storage) -20°C to +60°C
- Relative humidity 20% to 80%
- System MTBF 50K hrs (excluding CCFL 40K hrs)

* Resolution 1280x 1024, standard size, contrast max. brightness 50%, 9300°K, Full white pattern, without Audio.

We recommend using 1280 x 1024 at 60Hz non-interlaced mode for the best picture quality
As an Energy Star partner, Philips has determined that this product meets the Energy Star guidelines for energy efficiency. Microsoft and Windows are registered trademarks of Microsoft Corporation.
Macintosh is a registered trademark of Apple Computer, Inc.

All data subject to change without notice
Release date: January 2003
www.philips.com

