

17" TFT LCD SXGA monitor



Ultra Slim Frame

- 17-inch color LCD monitor with excellent display performance
- Standard VGA analog input
- Embedded AC power supply
- Advanced AUTO adjustment optimizes picture quality
- Adjustable tilt function



PHILIPS

17" TFT LCD SXGA monitor



Technical Specifications

LCD panel

- Type TFT LCD
- Screen size 17 inch / 43.2 cm
- Pixel pitch 0.264 x 0.264mm
- LCD panel type 1280 x 1024 pixels, R.G.B vertical stripe
- Anti-glare polarizer, hard coated
- Effective viewing area 337.9 x 270.3mm
- Display colors 16M colors

Scanning

- Vertical refresh rate 56~76 Hz
- Horizontal frequency 30~82 KHz

Video

- Video dot rate (Max.) 135 MHz
- Input impedance
 - video 75 ohm
 - Sync 2K ohm
- Input signal levels 0.7Vpp
- Sync input signal
 - Separate sync
 - Composite sync
 - Sync on green
- Sync polarities Positive and negative
- Video interface Analog (D-Sub) input

Optical characteristics

- Contrast ratio 400 (typ.)
- Brightness 260 cd/m² (typ.)
- Peak contrast angle 6 o'clock
- White chromaticity
 - x: 0.283 y: 0.297 (at 9300°K)
 - x: 0.313 y: 0.329 (at 6500°K)
- Viewing angle (C/R >5)
 - Upper ≥ 80° (typ.)
 - Lower ≥ 80° (typ.)
 - Left ≥ 80° (typ.)
 - Right ≥ 80° (typ.)
- Response time ≤25 ms (typ.)

Resolution & preset modes

- Maximum 1280x1024 at 75Hz
- Recommended 1280x1024 at 60Hz
- 33 user definable modes
- 15 factory preset modes:

	H.freq (KHz)	V.freq (Hz)
640 x 350	31.5	70
720 x 400	31.5	70
640 x 480	31.5	60
640 x 480	35.0	67
640 x 480	37.5	75
800 x 600	35.2	56
800 x 600	37.9	60
800 x 600	46.9	75
832 x 624	49.7	75
1024 x 768	48.4	60
1024 x 768	60.0	75
1152 x 870	69.0	75
1152 x 900	71.8	76
1280 x 1024	63.9	60
1280 x 1024	80.0	75

(Interlace mode is not applicable)

Plug and play compatibility

- Display data channel DDC 2B (VESA)
- Microsoft® Windows® 95/98/ Me & 2000/ XP compatible

Power management

Complies with EPA Energy Star and NUTEK specifications

- Typical operation 40W (typical)
- Sleep mode 1W

Low-emission characteristics

- Complies with TCO 99, MPRII and prEN50279 (so call MPRII) specifications

Monitor controls and functions

- Front
 - Power on/off - Tact Switch
 - OK - Tact Switch
 - Auto - Tact Switch
 - Up/Down - Tact Switch
 - (Brightness)
 - Left / Right - Tact Switch
- LED indicator
 - Green power on
 - Amber power save/OFF mode
 - Flashing Green new mode

Connections and cables

- Connections on monitor body
 - Video 15-pin D-sub (analog)
 - DC output 12V, 6.5mm DC connector
 - Power IEC/CEE-22 type male power inlet on monitor body
- Cables D-Sub video cable, Power cord

Regulatory approvals

- TUV/GS, TÜV-Ergo
- FCC-B, UL, CSA
- SEMKO
- prEN50279 Low Emission
- CE Mark
- NUTEK, Energy Star
- TCO '99

Physical specifications

- Dim. incl. base (WxHxD) 375 x 359 x 180 mm
- Dim. excl. base (WxHxD) 375 x 326 x 60 mm
- Tilt -5°~25°
- Weight 4.3 Kg
- Power supply 100 – 240 VAC, 50/60 Hz
- Power consumption 40 W* (typ.)
- Temperature (operating) +5°C to +35°C
- Temperature (storage) -20°C to +60°C
- Relative humidity 20% to 80%
- System MTBF 50K hrs (excluding CCFL 40K hrs)

* Resolution 1280x1024, standard size, contrast max., brightness 50%, 9300°K, Full white pattern.

We recommend using 1280 x 1024 at 60Hz non-interlaced mode for the best picture quality

As an Energy Star partner, Philips has determined that this product meets the Energy Star guidelines for energy efficiency. Microsoft and Windows are registered trademarks of Microsoft Corporation

Macintosh is a registered trademark of Apple Computer, Inc.

All data subject to change without notice

Release date: January 2003

www.philips.com

