



Philips
LCD monitor

43 cm (17")
SXGA

170V6FB

performance and convenience maximize your budget

This slim, compact 170V6 pumps up productivity with great performance and convenience while business-friendly features like low power consumption deliver the best total cost of ownership and lead-free design safeguards our environment.

Best total cost of ownership solution

- Lead-free design safeguards our environment
- Power consumption below the industry average
- TCO guarantees the highest safety and ergonomics standards
- Environmentally responsible Energy Star partner
- Kensington anti-theft lock-ready for added security

Outstanding front of screen performance

- 12ms On/off response time: Superior text and graphics display
- SXGA 1280 x 1024 resolution for sharper display
- sRGB ensures color matching between display and printouts

Great convenience

- Embedded power supply eliminates external power adaptors
- Easy, user friendly plug-and-play installation
- Auto adjustment for perfect picture display with one touch
- Convenient, built in holder for notes, cards or photos

PHILIPS
sense and simplicity

Highlights

Lead-free

Lead-free display products are designed and produced in compliance with strict European Community directives on Restriction of Hazardous Substances (RoHS) standards that restrict lead and other toxic substances that can harm the environment.

Lower power consumption

Reduction of the electrical power required to operate a device.

TCO '99 compliance

A TCO (Swedish Confederation of Professional Employees) standard even more stringent than MPR-II for safety and ergonomics, especially concerning alternating electric fields (AEF).

Kensington lock compatible

Small apertures built into the display's frame for use with a locking device that secures a display to a fixed object for added protection against theft.

12ms response time (On-Off)

On-Off response time is the period required for a liquid crystal cell to go from active (black) to inactive (white) and back to active (black) again. It is measured in milliseconds. Faster is better: Lower response time means faster transitions and, therefore, results in fewer visible image artifacts in the display of transition of text and graphics. On-Off response time is a more important measure in the display of business content like documents, graphs and photos.

sRGB ready

sRGB is an industry standard that ensures the best possible match between the colors displayed on your screen and those in your printouts.

Embedded power supply

An embedded power supply is a power adaptor built into the body of a display device that replaces a bulky external power adaptor.

Easy plug-and-play

Plug-and-play is a peripheral connectivity standard. A plug and play display device can be connected to a PC and operate without requiring user intervention to adjust complicated settings.

One-touch auto adjustment

The auto adjustment key restores optimal screen position, phase and clock settings with the press of a single button - without navigation through OSD menus and control keys.

FlexiHolder

FlexiHolder is a slim groove on the top of monitor that neatly and conveniently stores favorite photos, reminders, to-do lists or phone numbers in your line of sight.



Specifications

Picture/Display

- LCD panel type: 1280 x 1024 pixels, Anti-glare polarizer, RGB vertical stripe
- Panel Size: 17"/ 43 cm
- Effective viewing area: 337.9 x 270.3 mm
- Pixel pitch: 0.264 x 0.264 mm
- Brightness (nits): 250 nit
- Contrast ratio (typical): 500:1
- Display colors: 16.2 M
- Viewing angle: @ C/R > 5
- Viewing angle (H / V): 160 / 140 degree
- Response time (typical): 12 ms
- White Chromaticity, 6500K: $x = 0.313 / y = 0.329$
- White Chromaticity, 9300K: $x = 0.283 / y = 0.297$
- Maximum Resolution: 1280 x 1024 @ 75 Hz
- Optimum resolution: 1280 x 1024 @ 60 Hz
- Factory Preset Modes: 15 modes
- User definable modes: 50 modes
- Video Dot Rate: 140 MHz
- Horizontal Scanning Frequency: 30 - 83 kHz
- Vertical Scanning Frequency: 56 - 76 Hz
- sRGB

Connectivity

- Signal Input: VGA (Analog)
- Sync Input: Composite Sync, Separate Sync, Sync on Green

Convenience

- User convenience: On-screen Display
- Monitor Controls: Auto, Brightness Control, Left/Right, Menu (OK), Power On/Off, Up/Down
- OSD Languages: English, French, German, Italian,

- Simplified Chinese, Spanish
- Other convenience: Kensington lock compatible, FlexiHolder
- Plug & Play Compatibility: DDC/CI, sRGB, Windows 98/ME/2000/XP
- Regulatory approvals: CE Mark, E2000, EMC, Energy Star, FCC-B, UL, CSA, SEMKO, TCO '99, TÜV/GS, TÜV Ergo
- Tilt: -5° to 25°
- VESA Mount: 100 x 100 mm

Accessories

- Included accessories: AC Power Cord, VGA cable
- Optional accessories: Super Ergo Base
- User Manual

Dimensions

- Dimensions (with base) (W x H x D): 375 x 390 x 200 mm
- MTBF: 50,000 hrs
- Relative humidity: 20% - 80%
- Temperature range (operation): 5°C to 40°C
- Temperature range (storage): -20°C to 60°C
- Weight: 3.9 kg

Power

- Complies with: E2000, Energy Star, NUTEK
- Consumption (On mode): 30W (Typical)
- Consumption (Off Mode): < 1 W
- Power LED indicator: Operation - green, Stand by/ sleep - Amber
- Power supply: Built-in, 90-264 VAC, 50/60 Hz



Issue date 2011-06-07

Version: 1.0.3

12 NC: 8639 000 16382
UPC: 0 37849 96245 9

© 2011 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com