

Philips

17"

17HT3154



Compact ProPlus TV with Hotelmode

The ProPlus line offers a wide range of functions aimed at maximising management efficiency whilst guaranteeing the perfect convenience for guests

Advanced Hotel Mode

- Fast cloning - Wireless Smart Loader™
- External Loudspeaker Connector
- Welcome message on screen display
- Volume Control Locking
- Front Controls Locking
- Switch On Channel Programming
- Security Menu Access
- ESP™ (Energy Savings Programmability)
- Battery Low Detection for Remote Control
- Multi Language Teletext reception

Stylish design

- Compact, sleek design and small size fits in every room

PHILIPS
sense and simplicity

Specifications

Picture / Display

- Aspect ratio: 4:3
- Diagonal screen size: 17 inch / 43 cm
- Visible diagonal screen size: 41 cm
- Display screen type: Black Matrix picture tube
- Picture enhancement: Smart Picture
- Picture processing: 50 Hz

Sound

- Sound system: Mono
- Output power (RMS): 2W

Loudspeakers

- Built-in speakers: 1

Convenience

- Ease of installation: PLL digital tuning
- Ease of Use: Smart picture control
- Remote control type: RC2886
- Teletext: 1 page Teletext
- Clock: Sleep timer
- Remote control: TV
- Screen format adjustments: 4:3

Tuner / Reception / Transmission

- Tuner bands: Hyper band, S channel, UHF, VHF
- TV system: PAL B/G, PAL D/K, PAL I, SECAM B/G, SECAM D/K, SECAM L/L'

- Video playback: NTSC
- Aerial input: 75 ohm coaxial (IEC75)
- Number of preset channels: 125
- Antenna: FM antenna

Connectivity

- Number of scarts: 1
- Ext I Scart: CVBS in/out, RGB
- Front / Side connections: Headphone out
- Headphone: 3.5 mm
- Connectivity enhancements: External Loudspeaker connector, RJ12 Smartloader

Power

- Power consumption: 44 W
- Standby power consumption: < 5 w
- Mains power: AC 220 - 240 V +/- 10%

Dimensions

- Product weight: 14 kg
- Weight incl. packaging: 18 kg
- Colour cabinet: Blue silver
- Box dimensions (W x H x D): 540 x 475 x 520 mm
- Set dimensions (W x H x D): 422 x 396 x 405 mm

Product highlights

Wireless Smart Loader™

Provides the ability to copy easily and wirelessly all programming settings from one TV set into other TV sets in less than a minute. The feature ensures uniformity between TV sets and significantly reduces installation time and costs.

External Loudspeaker Connector

Amplified audio connector for easy installation of external speakers (like for bathrooms), eliminating the need for investments in external equipment

Welcome Message

Welcome greeting displayed on screen each time the TV set is switched on

Volume Control Locking

This feature predefines the volume range in which the TV set can operate, preventing excessive volume adjustments avoiding disturbance of next door neighbours.

Front Controls Locking

Prevents unauthorised access to TV functions

Switch On Channel Programming

It forces the TV set to a specified channel when turned on. Perfect for in-house advertising or information channels.

Security Menu Access

Provides conditional access to installation and configuration settings via a special code or master remote control

ESP™

Feature can be selected in the set-up menu. The TV can be switched off automatically after a specified period of use saving energy and providing extended product life time. The selectable range is from 0 to 99 hours.

Battery Low Detection

This feature informs of the need to replace the remote control batteries preventing unnecessary replacement of batteries.

Multi Language Teletext

Allows users to select their preferred language supported by the teletext characters



Date of issue 2007-01-03

Version: 3.0

12 NC: 8670 000 14516
EAN: 87 10895 71473 0

© 2007 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com