



Philips Matchline
Flat TV with Crystal Clear
III

43 cm (17")

LCD
Progressive Scan

MATCH /// LINE

17PF9945

Enhanced picture and sound

Get optimal picture quality with DCDi technology by Faroudja, Digital Comb Filter and a LCD panel with wide viewing angles. On top you also get built-in FM radio and a compact design, for the best value.

Vivid, natural and razor sharp images

- High-definition LCD XGA display, 1024 x 768p
- Crystal Clear III for natural images with enhanced quality
- Progressive Scan component video for optimized image quality
- Active Control optimizes picture quality whatever the source

Superb sound reproduction

- Virtual Dolby Surround for a cinema-like audio experience

Multi-purpose convenience

- The FM radio tuner enhances your personal enjoyment
- 100 pages of teletext for fast access to text information
- Twin page teletext allows simultaneous viewing of two pages
- VGA input so that you can also use your TV as a PC monitor
- View PC content in a second window on your TV

PHILIPS

Specifications

Picture/Display

- Aspect ratio: Widescreen
- Brightness: 450 cd/m²
- Contrast ratio (typical): 400:1
- Diagonal screen size: 17 inch / 43 cm
- Visible diagonal screen size: 43 cm
- Display screen type: LCD WXGA Active Matrix TFT
- Picture enhancement: 2D Combfilter, 3/2 - 2/2 motion pull down, Active Control, Color Transient Improvement, Color Temperature Adjustment, Contrast Plus, Crystal Clear III, Jagged Line Suppression, Luminance Transient Improver, Progressive scan, Sharpness Adjustment
- Screen enhancement: Anti-Reflection coated screen
- Viewing angle (H / V): 170 / 170 degree
- Panel resolution: 1280 x 768p
- Response time (typical): 25 ms

Supported Display Resolution

Computer formats

Resolution	Refresh rate
1024 x 768	60Hz
640 x 480	60, 72, 75, 85Hz
800 x 600	56, 60, 72, 75,85Hz
1280 x 768	60Hz

Video Formats

Resolution	Refresh rate
720 x 576i	1Fh
720 x 576p	2Fh

Sound

- Sound Enhancement: Ultra Bass
- Sound System: Mono, Nicam Stereo, Virtual Dolby Surround
- Total Sound Power (RMS): 12 W

Convenience

- Ease of Installation: Auto Program Naming, Automatic Channel Install(ACI), Automatic Tuning System (ATS), Autostore, Fine Tuning, Plug & Play, Program Name, Sorting
- Ease of Use: Auto Volume Leveller (AVL), FM Radio, Graphical User Interface, Program List, Smart Picture, Smart Sound
- Remote control type: RCAE039
- Teletext: 100 page Smart Text
- Teletext enhancements: 4 favourite pages,

- Program information Line
- Picture in Picture: Picture in graphics, Twin page text
- Remote Control: DVD, TV, VCR
- Screen Format Adjustments: Full screen, Subtitle and Heading Shift, Superwide, Widescreen, Zoom 14:9, Zoom 16:9
- Clock: Wake up Clock, Sleep Timer
- VESA Mount: 100 x 100 mm
- Child Protection: Child Lock

Tuner/Reception/Transmission

- Tuner bands: FM, VHF, UHF, S-Channel, Hyperband
- TV system: PAL, PAL I, PAL B/G, PAL D/K, SECAM, SECAM D/K, SECAM L/L', SECAM B/G
- Video Playback: NTSC, PAL, SECAM
- Aerial Input: 75 ohm coaxial (IEC75)
- Tuner Display: PLL
- Number of Preset Channels: 100

Connectivity

- Number of Scarts: 2
- Ext 1 Scart: RGB, CVBS in/out, Audio L/R
- Ext 2 Scart: S-video in, Y/C, CVBS in/out, Audio L/R
- Other connections: Audio constant level out, PC-in VGA + Audio L/R in, Antenna IEC75, FM Antenna
- Front / Side connections: Audio in, CVBS in, Headphone Out, S-video in

Power

- Power consumption: 55 W W
- Standby power consumption: < 3 W
- Ambient temperature: 5 °C to 40 °C
- Power supply: AC 90-240

Dimensions

- Product weight: 5 kg
- Dimensions (with base) (W x H x D): 517 x 307 x 65 mm

Accessories

- Included accessories: Power cord, Quick start guide, Registration card, Remote Control, RF antenna cable, User Manual
- AC/DC Adaptor/Charger: Multi-voltage

Highlights

LCD XGA display, 1024 x 768p

This XGA display with state-of-the-art LCD screen technology has a widescreen HD resolution of 1024 x 768p pixels. It produces brilliant flicker-free progressive scan pictures with optimum brightness and superb colors. This vibrant and sharp image will provide you with an enhanced viewing experience.

Crystal Clear III

Crystal Clear III combines a whole range of enhancements to provide a better picture. They include a 2D Comb filter, Dynamic contrast, Blue stretch and Green enhancement so that you always get the most natural looking colors.

Progressive Scan

Progressive Scan doubles the vertical resolution of the image resulting in a noticeably sharper picture. Instead of sending a field comprising the odd lines to the screen first, followed by the field with the even lines, both fields are written at one time. A full image is created instantaneously, using the maximum resolution. At such a speed, your eye perceives a sharper picture with no line structure.

Active Control

Active Control ensure that noise and sharpness improvements are continuously made at a rate of 60 times per second. By continually adjusting picture setting over 3,000 times per minute, Active Control Plus ensures that the viewing experience is optimized.

Virtual Dolby Surround

Virtual Dolby Surround is a processing technology for enhancing surround sound effects. It will create the sensation of Dolby Pro Logic without the necessity of additional rear speakers. You become totally immersed in your television experience.

FM-radio

A small FM radio is integrated into the headphone so you always have a music source with you.

100 page Smart Text

The teletext is a common system transmitted by most broadcasters. The 100 page smart text feature gives you fast access to information when changing pages.

Twin page teletext

Twin page teletext allows you to simultaneously view two teletext pages side by side

VGA input

The TV set has a VGA input which is compatible with the display output signal from your PC. This means you can use the set both as a TV and PC Monitor at your convenience.

Picture in Graphics

Picture-in-Graphics is a small window in the main picture, allowing to watch data/graphics in your main TV screen. It provides the ability to simultaneously watch data/graphics and the TV.



Issue date 2014-02-06

Version: 1.0.2

12 NC: 8670 000 19168
EAN: 87 10895 78170 1

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com