



Philips
LED monitor

V Line
18.5"/47 cm

196V3LAB

Enjoy great LED pictures in vivid colours

This attractive, slim display is a delight to use. Essential features like SmartContrast ensure rich bright images, and stereo speakers enhance your multimedia experience, making it a great choice!

Great picture quality

- LED technology for natural colours
- SmartContrast 10,000,000:1 for incredibly rich black details

Design that complements any interior

- Attractive slim, glossy design
- Small footprint to blend into any lifestyle

Greener every day

- Mercury Free eco-friendly display
- Energy Star for energy efficiency and low power consumption

Experience true multimedia

- Built-in speakers for audio without desktop clutter

Great convenience

- Easy display performance tuning with SmartControl Lite

PHILIPS

Highlights

LED technology

White LED's are solid state devices which light up to full, consistent brightness faster saving startup time. LED's are free from mercury content, which allows for eco-friendly recycling and disposal process. LED's allow for better dimming control of the LCD backlight, resulting in a super high contrast ratio. It also gives superior colour reproduction thanks to consistent brightness across the screen.

Built-in speakers

A pair of stereo speakers built into a display device. It can be visible front firing, or invisible down firing, top firing, rear firing etc, depending on model and design.

SmartContrast ratio 10,000,000:1

You want the LCD flat display with the highest contrast and most vibrant images. Philips

advanced video processing combined with unique extreme dimming and backlight-boosting technology results in vibrant images. SmartContrast will increase the contrast with excellent black level and accurate rendition of dark shades and colours. It gives a bright, lifelike picture with high contrast and vibrant colours.

SmartControl Lite

SmartControl Lite is the next generation 3D icon-based GUI monitor control software. This allows the user to fine-tune most parameters of the monitor like Colour, Brightness, screen calibration, Multimedia, ID management etc. with the mouse.

Mercury Free

Philips monitors with LED backlighting are free from Mercury, one of the most toxic natural

substances, which affects humans and animals. This reduces the environmental impact of the display throughout its lifecycle, from manufacturing to disposal.

Energy Star 5.0

Energy Star is a US EPA sponsored energy efficiency programme also adopted by many other countries. Energy Star certification ensures that you are buying a product which meets the latest power efficiency standards and which operates with maximum power efficiency at all operational levels. New Philips monitors are certified for Energy Star 5.0 specifications and meet or exceed the standard. For example, in sleep mode Energy Star 5.0 requires less than 1 Watt power consumption, whereas Philips monitors consume less than 0.5 Watts. Further details can be obtained from www.energystar.gov



Specifications

Picture/Display

- LCD panel type: TFT-LCD
- Backlight type: W-LED system
- Panel Size: 18.5 inch/47 cm
- Effective viewing area: 409.8 (H) x 230.4 (V)
- Aspect ratio: 16:9
- Optimum resolution: 1366 x 768 @ 60 Hz
- Response time (typical): 5 ms
- Brightness: 250 cd/m²
- SmartContrast: 10,000,000:1
- Contrast ratio (typical): 1000:1
- Pixel pitch: 0.30 x 0.3 mm
- Viewing angle: 170° (H)/160° (V), @ C/R > 10
- Display colours: 16.7 M
- Scanning Frequency: 30–83 kHz (H)/56–75 Hz (V)
- sRGB

Connectivity

- Signal Input: VGA (Analogue), DVI-D (digital, HDCP)
- Sync Input: Separate Sync, Sync on Green
- Audio (In/Out): PC audio-in

Convenience

- Built-in Audio: 1.5 W x 2
- User convenience: Auto, Volume, Brightness, Menu, Power On/Off
- OSD Languages: English, French, German, Spanish, Italian, Russian, Simplified Chinese, Portuguese, Turkish
- Other convenience: Kensington lock
- Plug and Play Compatibility: DDC/CI, Windows 7, Mac OS X, sRGB

Stand

- Tilt: -5/+20 degree

Power

- On mode: 13.42 W (EnergyStar 5.0 test method)
- Standby mode: 0.5 W
- Off mode: 0.5 W
- Power LED indicator: Operation - White, Standby mode - White (flashing)
- Power supply: Built-in, 100-240 VAC, 50/60 Hz

Dimensions

- Product with stand (mm): 463 x 358 x 204 mm
- Product without stand (mm): 463 x 284 x 44 mm
- Packaging in mm (W x H x D): 507 x 377 x 101 mm

Weight

- Product with stand (kg): 2.39 kg
- Product without stand (kg): 2.09 kg
- Product with packaging (kg): 3.36 kg

Operating conditions

- Temperature range (operation): 0°C to 40°C °C
- Temperature range (storage): -20°C to 60°C °C
- Relative humidity: 20%–80% %
- MTBF: 30,000 hour(s)

Sustainability

- Environmental and energy: EPEAT Silver, RoHS, EnergyStar 5.0, Lead-free, Mercury Free
- Recyclable packaging material: 100 %

Compliance and standards

- Regulatory Approvals: BSMI, CE Mark, SEMKO, GOST, TUV/GS, TUV Ergo, UL/cUL, FCC Class B, PSB, SASO, WEEE

Cabinet

- Colour: Black
- Finish: Glossy (front bezel)/Textured (rear cover)



Issue date 2022-04-21

Version: 7.0.2

12 NC: 8670 000 76493
EAN: 87 12581 60352 6

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com