



Philips Flashlights
Rechargeable docking
station

See clearly. Work better

Professional tool, designed for ultimate performance

We are working with experts to better understand how light affects worker performance in production environments. With these insights, we have created lighting solutions that generate safe work environments.

High resistance

- Robust housing, water and dust resistant



22001UVX1

PHILIPS

Specifications

Outer Carton

- Number of consumer packages: 2
- Outer carton (L x W x H): 46 x 33 x 17 cm
- Gross weight: 2.276 kg
- GTIN: 1 87 27900 38664 3

Convenience

- Shock Resistance: IK09

Power

- Battery life time: up to 6 hr

Highlights

Robust housing

The MDLS is IK07 shock resistant and IP54 water, dust and workshop solvent resistant. All these standards will provide you with a good level of robustness and will protect your MDLS from shocks, water, dust and workshop solvents.



Issue date 2017-01-18

Version: 2.0.2

12 NC: 9237 956 17104
EAN: 87 27900 38664 6

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com