



Philips  
LED solutions

T10

249304000KX2



## Next Generation T10 LED Retrofit

LED technology is everywhere...even in your car

Philips presents a new range of LEDs for interior lighting. These upgrades give drivers all the existing benefits of the current LED lighting range, and, in addition, it becomes hassle-free!

### Heat resistant

- Improved temperature resistance

### Better light output

- 4000 K bright white light

# PHILIPS

# Specifications

## Technical specifications

- Voltage: 24 V
- Wattage: 1 W
- Base: W 2.1 x D 9.5
- Application: Interior light
- Type: T10

## Packaging Data

- Packaging type: Blister

## Green Specifications

- Heavy metals: Cd free, Hg free, Pb free

249304000KX2

# Highlights

## Improved temperature resistance

Improved temperature resistance

## 4000 K bright white light



Standard

BlueVision ultra

4000 K bright white light



Issue date 2016-12-26

Version: 3.0.4

12 NC: 9237 959 20512  
EAN: 87 27900 38726 1

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)