



Philips Signage Solutions  
Multi-Touch Display

24"

Powered by Android  
Multi-touch

**SignageSolutions**

24BDL4151T



## Make it personal

Compact Multi-Touch display.

Promote. Inform. Intrigue. This clear, responsive Philips Multi-Touch Smart Display makes a superb all-in-one solution. Content is simple to manage remotely and it's easy to connect 4G modules. Power-over-Ethernet enables flexible placement

### Superb picture. Responsive touchscreen.

- Crisp contrast. High readability
- Plug-and-play 10-point Multi-Touch display
- Android 7 SoC processor. Native and web apps
- Built-in camera, mic, and speaker

### Effortless setup. Total control.

- Easy installation with PoE+ technology
- Operate, monitor and maintain with CMND & Control
- CMND & Create. Develop and launch your own content
- CMND & Deploy. Install and launch apps remotely

### Versatile system solution

- TeamViewer Host app. Remote control and screen sharing
- Integrated mPCIe slot for optional 4G/LTE module
- Internal memory. Upload content for instant play
- Flexible mounting: portrait, landscape, and table-top

**PHILIPS**

Multi-Touch Display  
24" Powered by Android, Multi-touch

# Highlights

## Powered by Android

Control your display via an Internet connection. Android-powered Philips Professional Displays are optimized for native Android apps, and you can install web apps directly to the display too. A built-in scheduler makes it easy to launch apps and content based on time of day.

## Built-in camera

The built-in camera, mic, and speaker make this small touchscreen a truly versatile smartsolution. Use it for retail audience measurement, footfall analytics, and more. Harness the power of Android AI apps to show targeted content. Or simply use your display for video conferencing.

## Power over Ethernet (PoE+).

Place your Philips Professional Display almost anywhere. PoE+ allows power and data to be delivered to your display over a single Ethernet

cable. You won't need a power socket, but a power adapter is also supplied should you wish to plug in.

## Internal memory

Save and play content without the need for a permanent external player. Your Philips professional display has an internal memory, which allows you to upload media into the display for instant playback. The internal memory also functions as a cache for online streaming.

## CMND & Create



Take control of your content with CMND & Create. A drag-and-drop interface makes it simple to publish your own content-whether it's

24BDL4151T/00

a daily specials board or branded corporate information. Preloaded templates and integrated widgets ensure your stills, text, and video will be up and running in no time.

## CMND & Control



Run your display network over a local (LAN) connection. CMND & Control allows you to perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.

# Specifications

## Picture/Display

- Diagonal screen size: 23.6 inch / 59.94 cm
- Optimum resolution: 1920 x 1080
- Brightness: 210 cd/m<sup>2</sup>
- Contrast ratio (typical): 1000:1
- Aspect ratio: 16:9
- Response time (typical): 5 ms
- Viewing angle (H / V): 170 / 160 degree
- Display colors: 16.7 M

## Operating system

- Operating System: Android 7.1.2

## Internal Player

- CPU: RK3399, T5080
- Memory: 4GB DDR3
- Micro SD Card Slot: Micro SD ver2.0 (SD/SDHC card upto max 128GB)
- Internal memory storage: 16GB EMMC

## Camera

- Camera: Built-in 2MP/1080P (1920 x 1080)

## Sound

- Built-in speakers: 2 x 2W

## Communication

- Wi-Fi/ WLAN: On board IEEE802.11 b/g/n/ac 2.4/5 GHz
- External 4G mPCIe slot

## Connectivity

- Other connections: micro SD
- USB: USB 2.0 x 1, USB 3.0 x 1 w/fast charging
- Audio output: 3.5 mm Mini Jack (x1)
- External control: RJ45
- Video input: HDMI
- Video output: HDMI

## Convenience

- Keyboard control: Hidden, Lockable
- Other convenience: G sensor for Auto-rotation
- Network controllable: RJ45, WiFi

## Power

- Mains power: 100 - 240V~, 50 - 60Hz, 1.5A
- Standby power consumption: <0.5W
- Consumption (Typical): 25 W
- PoE + (Power over Ethernet): 44-57V DC. 1.2A
- Consumption (Max): 45 W
- Energy Label Class: G

## Regulatory approvals/ Others

- Regulatory approvals: IEC 60950 class A, CB, CCC, CE, C-Tick, FCC, Class A, GS, PSE, TUV, UL
- Warranty: 3 years (where applicable)

## Accessories

- Stand: desktop stand (Landscape only)
- Included accessories: DC power adapter, HDMI cable, Power plug, Quick start guide, USB cable
- Included Accessories: Screws for 4G module board(2pc), Screws for Stand (4pcs), Wire Clamper (2pcs)

## Operating conditions

- Temperature range (operation): 0-45 °C
- Relative humidity: operating:30% ~ 80%, storage:10%-85% %
- MTBF: 50,000 hour(s)
- Altitude: 0 ~ 3000 m
- Temperature range (storage): -10 ~ 60 °C

## Miscellaneous

- On-Screen Display Languages: Arabic, English, French, German, Italian, Japanese, Polish, Spanish, Turkish, Russian, Simplified Chinese, Traditional Chinese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish

## Dimensions

- Set dimensions (W x H x D): 566.50 x 361.10 x 49.20 mm
- Product Weight: 4.7 kg
- VESA Mount: 100 x 100 M4
- Set dimensions in inch (W x H x D): 22.3 x 14.22 x 1.94 inch
- Bezel width: 22.6mm (L/R), 30.8(T), 33.9(B)
- Product weight (lb): 10.36 lb


## Multimedia Applications

- USB Playback Audio: AAC, M4A, MP3, WMA
- USB Playback Picture: BMP, JPEG, PNG
- USB Playback Video: ASF, AVI, DAT, FLV, MKV, MP4, MPEG, MPG, TS, VOB, WEBM, WMV

## Supported Display Resolution

### • Computer formats

Resolution	Refresh rate
1024x768	60,70Hz
1280 x 1024	60,67 Hz
1280 x 768	60Hz
1920 x 1080	60Hz
640 x 480	60Hz
640 x 480	72 Hz
800 x 600	56, 60, 72, 75Hz



Issue date 2022-05-15

Version: 5.0.2

12 NC: 8670 001 53885  
EAN: 87 12581 75221 7

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)