

Philips 5500 series LED TV

60 cm (24") LED TV Pixel Plus HD



24PHS5537

The motorhome TV

LED TV

Looking for a compact TV that performs big? Kitchen to bedroom to motorhome, this attractive TV goes anywhere! The sharp, vibrant picture ensures you'll enjoy everything you watch. You can even take it on the road thanks to the 12 V input

Looks great. Goes anywhere.

- Minimalist bezel and stand. Slender feet.
- Designed for smaller spaces. Packed for the future.
- 12V input. Perfect for motorhomes and campers.

Brilliant color. Surprising depth.

- Vibrant viewing. Philips LED TV.
- Pixel Plus HD. Sharp images, no matter what the source.

Plug and play. Whatever the source.

- Connections for everything you love.
- 2x HDMI ports. 1x USB port.
- \bullet VGA. Connect to retro gaming consoles or legacy PCs.



Specifications

Picture/Display

- Display: LED HD TV
- Diagonal screen size (metric): 60 cm
- Panel resolution: 1280x720 (720p)
- Native refresh rate: 60 Hz
- · Aspect ratio: 16:9
- Picture enhancement: Pixel Plus HD, Micro Dimming

Supported Display Resolution

- Computer inputs: up to 1366x768 @ 60Hz
- Video inputs: up to 1366x768p

Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- HEVC support

Power

- Mains power: AC 220 240 V 50/60Hz
- Standby power consumption: <0.3W
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)

Sound

- Output power (RMS): 6W
- Sound Enhancement: Incredible Surround, Clear Sound, Bass Control, Auto Volume Leveler, Dolby Bass Enhancement
- Speaker configuration: 2x3W full range speaker

Connectivity

- Number of HDMI connections: 2
- Number of USBs: 1
- Other connections: Common Interface Plus (CI+), Digital audio out (optical), Headphone out, Service connector, Antenna F-type, Audio in (VGA/DVI)
- EasyLink (HDMI-CEC): Remote control passthrough, System audio control, System standby, One touch play
- HDMI ARC: Yes on HDMI1

User Interaction

- Program: Pause TV
- Electronic Program Guide*: 8days Electronic Program Guide

Multimedia Applications

- Video Playback Formats: H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, HEVC
- Subtitles Formats Support: .SMI, .SRT, .SSA, .SUB, .TXT, .ASS
- Music Playback Formats: AAC, MP3, WAV, WMA (v2 up to v9.2)
- Picture Playback Formats: JPEG, BMP, GIF, PNG

Design

- Colors of TV: White gloss bezel
- Stand design: White round sticks

Dimensions

- Box dimensions (W x H x D): 710.0 x 425.0 x 132.0 mm
- Set dimensions (W x H x D): 551.5 x 333.1 x 82.0 mm
- Set dimensions with stand (W x H x D): $551.5 \times 356.6 \times 148.0 \text{ mm}$
- Stand dimensions (W x H x D): 445.5 x 23.5 x 148.0 mm
- Product weight: 3.0 kg
- · Product weight (+stand): 3.1 kg
- Weight incl. Packaging: 4.8 kg
- Wall mount compatible: 75 x 75 mm

Accessories

 Included accessories: Remote Control, 2 x AAA Batteries, Power cord, Quick start guide, Legal and safety brochure, Table top stand

EU Energy card

- EPREL registration numbers: 1133971
- Energy class for SDR: E
- On mode power demand for SDR: 17 Kwh/1000h
- Networked standby mode: n.a. W
- Off mode power consumption: n.a. W
- Panel technology used: LED LCD









Connections

Side

COMMON INTERFACE



TV ANTENNA



Rear





Bottom













Issue date 2023-02-04

Version: 8.1.1

All Rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

12 NC: 8670 001 82202 EAN: 87 18863 03380 7

www.philips.com

© 2023 Koninklijke Philips N.V.

Highlights

Design

Minimalist bezel and stand. Slender feet.

LED TV

Love everything you watch on this LED TV. Philips Pixel Plus HD engine optimizes picture quality to deliver sharp images, rich colors, and smooth motion. You get the best possible viewing experience every time.

Versatile connections

Plug a dongle into one of the TV's HDMI ports and enjoy smart TV features from your favorite streaming providers. You can use the USB port to play music from a USB drive, and you can even connect to retro consoles or legacy PCs via VGA.

- * EPG and actual visibility (up to 8 days) is country and operator
- dependent.

 * The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscripction are required. Contact your operator for more information.
- * This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.