



Philips
professional TV

64 cm (25")
real flat

25HT3317

SmartCard System TV

Designed for in-room interactive applications

The SmartCard System range provides the perfect combination of management efficiency and guest comfort. The integrated SmartCard slot allows expandability for interactive systems, is future proof and prepared for digital applications.

Best total cost of ownership

- Wireless SmartLoader for fast cloning
- Installation menu locking
- ESP™ (Energy Savings Programmability)
- Battery Low Detection for Remote Control
- External loudspeaker connector

Maximum guest comfort

- Welcome message on screen display
- Volume limitation

System ready and future proof

- Tamper proof SmartCard slot
- Smartplug RJ12 connector

Great viewing experience and guest comfort

- Real Flat picture tube technology brings you lifelike images
- Smart Picture and Smart Sound to personalize your viewing

PHILIPS

Highlights

Wireless SmartLoader

Provides the ability to copy easy and wireless all programming settings from one TV set into other TV sets in less than a minute. The feature ensures uniformity between TV sets and significantly reduces installation time and costs.

Installation menu locking

Prevents unauthorized access to installation and configuration settings, to ensure maximum guest convenience and avoid unnecessary reprogramming costs.

ESP™

Feature can be selected in the set-up menu. The TV can be switched off automatically after a specified period of use saving energy and provide extended product life time. The selectable range is from 0 to 99 hours.

Battery Low Detection

This feature informs of the need to replace the remote control batteries preventing nuisance calls and unnecessary replacement of batteries.

External loudspeaker connector

Amplified audio connector for easy installation of external speakers (like for bathrooms), eliminating the need for investments in external equipment

Welcome message

A welcome greeting is displayed each time the TV set is switched on.

Volume limitation

This feature predefines the volume range with which the TV set is allowed to operate, preventing excessive volume adjustments and avoiding disturbance of next door guests.

Integrated SmartCard Slot

The integrated SmartCard slot allows third parties to add new functionality to the TV through application cards, without the need for additional boxes and external connections. The TV can also be connected to external decoders and set-top boxes of all major interactive system providers, through the SerialXpress Control Interface (supporting UART and RS232 protocols) and the SmartPlug Control interface.

Smartplug RJ12 connector

The Smartplug RJ12 connector permits OEM or 3rd party decoders and controllers to interface with the TV.

Real Flat picture tube

The flatter tube provides a wider viewing angle while minimizing reflections for the best picture possible.



Specifications

Picture/Display

- Display screen type: Real Flat picture tube
- Diagonal screen size: 25 inch / 63 cm
- Aspect ratio: 4:3
- Picture processing: 50 Hz
- Color cabinet: Silver Frost

Sound

- Output power (RMS): 2 x 5 W
- Sound System: Stereo
- Sound Enhancement: Auto Volume Leveler, Incredible Surround, Dynamic Bass Enhancement

Loudspeakers

- Built-in speakers: 2

Tuner/Reception/Transmission

- Tuner bands: UVSH
- TV system: PAL B/G, PAL D/K, PAL I, SECAM B/G, SECAM D/K, NTSC
- Stereo System: Nicam BG/DK/I, 2CS BG/DK
- Video Playback: PAL, SECAM, NTSC
- Aerial Input: 75 ohm coaxial (IEC75)
- Number of Preset Channels: 125

Connectivity

- AV 2: CVBS, Y/C, YPbPr, Audio L/R in
- Front / Side connections: CVBS in, S-video in, Audio L/R in, Headphone Out
- Connectivity Enhancements: RJ12 SmartPlug connector, SmartCard Expansion Slot, External

- Loudspeaker connector
- Other connections: Monitor out

Convenience

- Ease of Installation: Automatic Tuning System (ATS), Fine Tuning, Cloning of TV settings, Advanced Hotel Mode, Program Name
- Ease of Use: Smart Picture, Smart Sound
- On-Screen Display languages: English, Malay, Simplified Chinese
- Comfort: Hotel Guest features
- Teletext: 10 page Smart Text
- Clock: On main display, Sleep Timer
- Remote Control: TV
- Remote control type: RC2887

Power

- Mains power: AC 90-276V, 50/60Hz
- Power consumption: Normal Operation 72 W

Dimensions

- Set weight: 31.5 kg
- Weight incl. Packaging: 35 kg
- Set dimensions (W x H x D): 622 x 523 x 458 mm
- Box dimensions (W x H x D): 718 x 619 x 562 mm

Accessories

- Included accessories: Remote Control, Batteries for remote control
- Optional accessories: Set up Remote RC2573GR, Wireless SmartLoader 22AV1120



Issue date 2020-05-06

Version: 1.0.2

12 NC: 8670 000 20456
EAN: 87 10895 82781 2

© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com