

Philips  
professional TV

64 cm (25")

25HT5405



## System SmartCard TV

Designed for in-room Interactive applications

The System SmartCard range provides management efficiency and perfect convenience for guests. The integrated extension slot allows expandability for interactive systems. It is Future proof and prepared for digital applications.

### **Interactive System Prepared, Future Proof**

- SmartCard 3v3 Expansion Slot
- Smartplug RJ12 connector

### **Advanced hotel features and future proof**

- Integrated clock display with wake up and message alarm
- Wireless SmartLoader for fast cloning
- External loudspeaker connector
- Welcome message on screen display
- Volume limitation
- Front Controls Locking
- Switch On Channel Programming
- Security Menu Access
- ESP™ (Energy Savings Programmability)
- Multi Language Teletext reception

# PHILIPS

# Specifications

## Picture/Display

- Aspect ratio: 4:3
- Diagonal screen size: 25 inch / 63 cm
- Color cabinet: Metallic Anthracite
- Visible diagonal screen size: 59 cm
- Display screen type: Blackline FX picture tube
- Picture enhancement: Sharpness Adjustment
- Picture processing: 50 Hz

## Sound

- Sound System: Nicam Stereo
- Output power (RMS): 2 x 5 W

## Loudspeakers

- Built-in speakers: 2

## Convenience

- Ease of Installation: Fine Tuning, PLL Digital Tuning
- Ease of Use: Smart Picture, Smart Sound
- Remote control type: RC86702 (not included)
- Teletext: 10 page Smart Text
- Screen Format Adjustments: 4:3
- Clock: Sleep Timer, Smart Clock

## Tuner/Reception/Transmission

- Tuner bands: Hyperband, S-Channel, UHF, VHF

- TV system: PAL B/G, PAL D/K, PAL I, SECAM B/G, SECAM D/K, SECAM L/L', SECAM
- Video Playback: NTSC
- Aerial Input: 75 ohm coaxial (IEC75)
- Number of Preset Channels: 127

## Connectivity

- Ext 1 Scart: CVBS in/out, RGB
- Connectivity Enhancements: RJ12 SmartPlug connector, SmartCard Expansion Slot, External Loudspeaker connector

## Power

- Mains power: AC 220 - 240 V +/- 10%
- Power consumption: 61 W
- Standby power consumption: 4W
- Consumption (Off Mode): 2.5 W

## Dimensions

- Product weight: 29 kg
- Weight incl. Packaging: 34 kg
- Box dimensions (W x H x D): 775 x 645 x 550 mm
- Set dimensions (W x H x D): 690 x 541 x 452 mm

# Highlights

## SmartCard 3v3 Expansion Slot

Permits OEM or 3rd party decoders and controllers to be installed inside the television for custom designed component integration. Eliminates the need for external set-top decoders, controllers, or data terminals. Integrates system for superior control applications. Allows expandability for future upgrades. Prepared for digital applications.

## Smartplug RJ12 connector

The Smartplug RJ12 connector permits OEM or 3rd party decoders and controllers to interface with the TV.

## Integrated clock display

The built-in clock display, which is also a wake-up alarm, eliminates the need and investment for an additional clock with cables and connections in the room.

## Wireless SmartLoader

Provides the ability to copy easy and wireless all programming settings from one TV set into other TV sets in less than a minute. The feature ensures uniformity between TV sets and significantly reduces installation time and costs.

## External loudspeaker connector

Amplified audio connector for easy installation of external speakers (like for bathrooms), eliminating the need for investments in external equipment

## Welcome message

A welcome greeting is displayed each time the TV set is switched on.

## Volume limitation

This feature predefines the volume range with which the TV set is allowed to operate, preventing excessive volume adjustments and avoiding disturbance of next door guests.

## Front Controls Locking

Prevents unauthorised access to TV functions

## Switch On Channel Programming

Perfect for in-house advertising or information channels as it allows to show a predefined channel when the TV is turned on.

## Security Menu Access

Provides conditional access to installation and configuration settings via a special code or master remote control

## ESP™

Feature can be selected in the set-up menu. The TV can be switched off automatically after a specified period of use saving energy and provide extended product life time. The selectable range is from 0 to 99 hours.

## Multi Language Teletext

Allows users to select their preferred language supported by the teletext characters

