

Philips
Healthcare LCD TV

66 cm (26")

LCD Pro: Idiom™

26HFL5830H

# Healthcare HD LCD TV

w/MPEG-4, SmartCard, Pro:Idiom™ & SmartWindow PIP

This HealthCare LCD TV delivers a superior picture with razor sharp images and brilliant colors. Designed for Hospital use, this set is TigrNet enabled and complete with Pro:Idiom and SmartCard, SmartPort and XpressIO connections.

# Designed for hospital use

- TigrNet<sup>™</sup> enabled
- XpressIO Port
- UL Approved for hospital use
- Integrated pillow speaker interface

# Integrated system solution and future proof

- HD content protection with  $\operatorname{Pro:Idiom^{TM}}$  Plus
- Compatible with all major PPV systems
- · New embedded prepaid solutions

# **B**est total cost of ownership

- Five Star Service two-year advanced exchange warranty
- SmartPower<sup>2</sup> and ESP for energy savings

## Sustainable and safe

- Eco-friendly Design
- Flame retardant housing



# Highlights

# TigrNet™ enabled

TigrNet<sup>™</sup> software provides a user interface and enhanced functionality to the patient television. TigrNet<sup>™</sup> can be used with a variety of products including TIGR education on-demand and upgraded services for subscription billing. TigrNet<sup>™</sup> provides access to The Internet, e-mail, hospital services, patient education, surveys, television, games and movies. TigrNet<sup>™</sup> allows monitoring from a central location using remote management software.

## **XpressIO Port**

XpressIO enables two-way communication with external control devices, including Tigr $Net^{TM}$ .

### **UL** Approved for hospital use

This set is specifically engineered to meet the more stringent requirements for use in hospital environments.

# Integrated pillow speaker inte

An easy to use and configure isolated interface for pillow speakers is built right into the TV.

### **Pro:Idiom™ Plus**

Pro:Idiom™ was created for the hospitality industry to protect first run movies and other HD premium content from piracy. Philips

Pro:Idiom™ Plus televisions offer secure HD content protection not only for PPV hotels, but now also for stand alone properties. (Additional fees may apply for stand alone use) (Pro:Idiom™ is a trademark of the Zenith Corp.)

# **PPV** system compatible

Philips Hospitality sets are designed to be compatible with all major Pay Per View systems, including, but not limited to, LodgeNet, OnCommand, NxTV, GuesTek, nStreams, Hospitality Network, and KoolConnect. This guarantees seamless integration in almost any system configuration.

### New embedded prepaid solutions

Philips Hospitality sets now support SmoovieTV<sup>TM</sup>, a completely new way to offer in room programming optimized for hotels that traditionally have not been able to charge for such amenities due to their size or budget. Simple to use, SmoovieTV<sup>TM</sup> requires no expensive head end equipment or in-room control boxes.

### **Five Star Service**

Philips offers unmatched commitment to keeping your guest rooms in working order. Our products are so reliable that we offer a two-year advanced exchange warranty. In the

event that something does go wrong, we guarantee to ship a replacement set to you, within 72 hours during the first year.

# SmartPower<sup>2</sup> and ESP

Our second generation power saving technology allows the backlight intensity to be dynamically adjusted by the system to reduce the power consumption by up to 60%, saving substantially on energy costs. In addition, Philips' Energy Savings Programmability (ESP) allows the set to turn itself off when not in use to save even more energy when guests or maids leave televisions on for long periods while the room is vacant.

### **Eco-friendly Design**

Philips TVs are designed and produced according to our EcoDesign principles aimed at minimizing overall environmental impact, through lower power consumption, removal of hazardous substances, lower weight, more efficient packaging and better recyclability.

### Flame retardant housing

Philips TVs have a special housing of flame retardant material. Independent tests carried out by emergency fire services have shown that whereas TVs can sometimes intensify fires caused by external sources, Philips TVs will not contribute to the fire.













# Specifications

# Picture/Display

- Aspect ratio: 16:9, Widescreen
- · Color cabinet: Black
- Brightness: 500 cd/m<sup>2</sup>
- Contrast ratio (typical): 800:1
- Dynamic screen contrast: 6400:1
- Diagonal screen size: 26 inch / 66 cm
- Picture enhancement: Pixel Plus 3 HD, Progressive scan, 3/2 - 2/2 motion pull down, Active Control, 3D Combfilter, Dynamic contrast enhancement, Contrast Plus, Digital Noise Reduction, Jagged Line Suppression, Luminance Transient Improver, Color Transient Improvement, Automatic skin tone correction, Color Enhancement, Motion adaptive de-interlacing
- Screen enhancement: Anti-Reflection coated
- Display screen type: LCD WXGA Active Matrix TFT
- Panel resolution: 1366 x 768p
- Response time (typical): 8 ms
- Viewing angle (H / V): 160 / 160 degree

# **Supported Display Resolution**

Computer formats

Video formats

 Resolution
 Refresh rate

 480i
 60Hz

 480p
 60Hz

 720p
 60Hz

 1080i
 60Hz

 1080p
 24, 25, 30Hz

 1080p
 24, 50, 60Hz

### Sound

- Sound System: Stereo, Dolby Digital (AC-3)
- Output power (RMS): 2 x 10W
- Sound Enhancement: Auto Volume Leveller, Incredible Surround

# Loudspeakers

• Built-in speakers: 2

# Convenience

- Ease of Installation: Fine Tuning, PLL Digital Tuning, Program Name, Advanced Hotel Mode, Cloning of TV settings via USB, Keyboard lock-out, Security menu access
- Ease of Use: Auto Volume Leveller (AVL), Smart Picture, Smart Sound
- Screen Format Adjustments: 4:3, 7 Widescreen Modes
- Comfort: Hotel Guest features, Sleep timer, Switch on channel, Volume limitation, Welcome message
- User convenience: Closed captioning (digital), Vchip and parental lock

- Interactive hotel features: Smoovie Pay TV
- Other convenience: Kensington lock

# Tuner/Reception/Transmission

- Tuner bands: Hyperband, S-Channel, UHF, VHF
- TV system: NTSC, ATSC
- · Video Playback: NTSC, PAL
- Number of Preset Channels: 250
- Cable: Unscrambled Digital Cable -QAM
- Terrestrial: ATSC (8VSB)
- Aerial Input: 75 ohm F-type

### Connectivity

- AV 1: AV In, S-Video Y/C
- AV 2: Audio L/R in, YPbPr
- AV 3: VGA PC-in, Audio-in mini jack 3.5mm
- Connectivity Enhancements: SmartCard Expansion Slot, HM-Link, Extra Power supply 12V/1W, USB2.0, RJ12 SmartPlug connector
- Audio Output Digital: Coaxial (cinch)
- Other connections: Antenna F-type, RS232 Serial
- AV 4: HDMI
- AV 5: HDMI

#### Power

- Power consumption: 125 W
- Mains power: 110 240V, 50/60Hz
- Ambient temperature: 5 °C to 40 °C
- Standby power consumption: 1.12 W
- Power use SmartPower<sup>2</sup> = high: < 40 watts
- Power use SmartPower<sup>2</sup> = off: < 115 watts

### **Dimensions**

- Set dimensions in inch (W  $\times$  H  $\times$  D): 26.7  $\times$  18.6  $\times$  4.5 inch
- Box dimensions in inch (W x H x D): 22.6 x 8 x 33.1 inch
- Product weight (lb): 25.3
- Weight incl. Packaging (lb): 29.8
- VESA wall mount compatible:  $200 \times 100 \text{ mm}$

### Accessories

- Included accessories: 3.5mm to 6.3mm jack cable, Power cord, Warranty Leaflet
- Optional accessories: Set up Remote RC2573GR, Mounting brackets/ stands, Table top Stand with Swivel

# **Multimedia Applications**

- Multimedia connections: USB
- Playback Formats: JPEG Still pictures, MP3, Slideshow files (.alb)

### **Green Specifications**

- Safety: Flame retardant housing
- Eco Designed
- SmartPower<sup>2</sup>

### Healthcare

- Control: Pendant control connector
- Convenience: Independent main speaker mute
- Safety: Galvanic isolated connections, Grounded power cord



Issue date 2011-06-07

Version: 5.1.12

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

12 NC: 8670 000 37501 UPC: 6 09585 15023 2

www.philips.com

\* Five Star Advanced Exchange warranty is valid in the United States only. Local warranties govern sales in other countries.